


Model : V20C13/4C19-32A-W/F_EN/3B-1

EMEA code : AHV000201042343111




Safety Regulatory :
Environmental :

Cordset : 3 meter 4mm sq H05V V-F cable with IEC60309 32A 2P + E plug
Fuse : 2 x 16A Resettable Fuse
Input Rating : 32A / 250Vac

For 32A Rating PDU, the models which have 24 socket outlets,
< CIRCUIT A > Socket #1-10 C13 & #C1-C2 C19 socket outlets can only output 16A maximum.
< CIRCUIT B > Socket #11-20 C13 & #C3-C4 C19 socket outlets can only output 16A maximum.

Model : V20C13/4C19-20A-W/F_OE/3B-1

EMEA code : AHV000201042543511



Cordset : 3 meter 2.5mm sq H05V V-F cable with 20 Amp open-end
Fuse : 1 x 20A Resettable Fuse
Input Rating : 20A / 250Vac


Model : V20C13/4C19-16A-W/F_EN/3B-1

EMEA code : AHV000201042243111

OR

V20C13/4C19-16A-W/F_C20/3B-1

AHV000201042243211



Cordset : 3 meter 1.5mm sq H05V V-F cable with IEC60309 16A 2P + E or IEC320 C20 plug
Fuse : 1 x 16A Resettable Fuse
Input Rating : 16A / 250Vac

UNIT : mm

Common Specification :

Description : 20 outlets IEC320 C13, 4 outlets IEC320 C19
Receptacles : 20 outlets IEC320 C13 10A Rated, 4 outlets IEC320 C19 16A Rated
Meter : RMS digital ammeter measuring input load current

PDU Dimension : 60 (W) x 50 (D) x 1350 (H) mm
Packing :

Net Weight :
Gross Weight :

WARNING : The individual user should take care to determine prior to use whether this device is suitable, adequate or safe for the use intended. Since individual applications are subject to great variation, the manufacturer makes no representation or warranty as to the suitability or fitness of these devices for any specific application.

The company reserves the right to modify product specifications without prior notice and assumes no responsibility for any error which may appear in this publication.

Copyright 2013 Austin Hughes Electronics Ltd. All rights reserved.