



Tsunami® QB-8200 Series

Wireless Product Portfolio

- **Tsunami® 8200 Series**

PtP & PtMP product line delivering 300 Mbps plus data rate

- **Tsunami® 800 Series**

Compact and robust, high performance, PtP & PtMP product line

- **Tsunami® .11 Series**

Our best selling Point-to-point and multipoint product line

- **Tsunami® GX-810 Series**

Carrier-class IP Ethernet bridge for voice and data backhaul for service providers and enterprise applications

- **ORiNOCO® AP 8000 Series**

The industry's highest performance 802.11a/b/g/n access points

Proxim Wireless is a global pioneer of broadband wireless systems that deliver the quadruple play of video, voice, data and mobility. Regardless of the application, our end-to-end product portfolio enables partners to custom-build the wireless solution that fits customer's specific needs. Our point-to-point wireless backhaul products are available through our extensive global channel networks.

Next generation of field-proven Tsunami QuickBridge® 8000 Wireless Backhaul Solution that Exceeds 4G Speed Requirements with 300 Mbps data rate!

The Tsunami® QB-8200, is a high power, extremely reliable and a cost-effective, non-line-of-sight 4G point-to-point (PtP) wireless backhaul solution. It delivers data rates of 300 Mbps, along with excellent spectrum and 25.8 dBm high power radios for extend coverage.

With its incredible channel capacity & flexibility, excellent spectrum efficiency and a highly evolved prioritization platform tailored to deliver voice, video and data applications, the Tsunami® QB-8200 satisfies carriers, wireless service providers and Government organizations with requirements for fast and reliable wireless backhaul.

The Tsunami® QB-8200 leverages the advantages of OFDM, MIMO radio innovations and Proxim's proprietary Wireless Outdoor Routing Protocol (WORP®) to provide wireless performance in excess of 4G products on the markets today.

World-class Performance

- Point-to-Point system that delivers 300 Mbps data rate at distances of over 5 miles (8 km)
- Very low latency of 2 to 3 ms to support voice and video applications over long distances
- Dual IPv4 and IPv6 stack for transparent evolution to tomorrow networks
- Built-in feature rich network protocols for bridging, routing and gateway functionality

Non-Line-of-Sight and Advanced Features

- Non-line-of-sight capable, utilizing OFDM and enhanced 3x3 MIMO techniques to better penetrate through obstructions
- Features dual Gigabit Ethernet ports with PoE out to power other devices like surveillance cameras or additional radios
- Enables packet identification to create unique and sophisticated service rules and tiered service classes with ease
- Compatibility with LACP switches for link aggregation
- Spectrum analyzer to help study frequency bands for interference, and select a relatively low interference channel.

Frequency Agnostic

- Operates in licensed and unlicensed frequency bands
- Flexible channel planning with 5, 10, 20 and 40MHz size
- Provides support for extended frequency bands from 4.900 to 5.925 GHz

Carrier-Grade Security

- Implements tiered security layers for the most secure outdoor wireless communications in the unlicensed frequency spectrum
- Utilizes Proxim's Wireless Outdoor Routing Protocol (WORP®), which prevents snooping, and features highly-secure remote management via SSL, SSH and SNMPv3
- Provides military-grade security with AES encryption technology, prevents unsecure client-to-client communications and leverages MAC, Ethertype and IP address packet filtering for granular network security

Cost Effective and Ease of Use for Quick Return on Investment

- Suitable for the carriers, WISP and Government markets
- Certified for deployments in the Americas, Europe and Asia
- The most cost-effective, high performance point-to-point solution from Proxim, enabling any deployment to enjoy a quick return on investment

Product Line Compatibility

- Connects to existing Tsunami® QB-8100

PRODUCT MODELS					
QB-8200-LNK	Tsunami® QB 8200 Link, 300 Mbps, MIMO 3x3, Type-N Connectors (Two QB-8200-EPA)				
QB-8250-LNK	Tsunami® QB 8250 Link, 300 Mbps, MIMO 2x2, 23 dBi Integrated Antenna (Two QB-8250-EPR)				
INTERFACES					
WIRED ETHERNET	Two auto MDI-X RJ45 10/100/1000Mbps Ethernet - Port #1 with PoE in & Data - Port #2 with PoE out (802.3af pin out) & Data				
WIRELESS PROTOCOL	WORP® (Wireless Outdoor Router Protocol)				
RADIO & TX SPECS					
MIMO	3x3MIMO				
MODULATION	OFDM				
FREQUENCY	4.900 – 5.925 GHz (Subject to Country Regulations)				
CHANNEL SIZE	40 MHz, 20 MHz, 10 MHz*, 5 MHz* channel bandwidths			* Not applicable for DFS Band	
DATA RATE	MCS 0 to 15 for High Throughput mode (6.5 – 300 Mbps) with Dynamic Data Rate Selection				
TX POWER	Up to 25.8 dBm (Triple chain)				
TX POWER CONTROL	0 – 25 dB, in 0.5 dB steps. Automatic TPC with configurable EIRP limit				
RX SENSITIVITY (PER=10%)	Channel Size	40 MHz	20 MHz	10 MHz	5 MHz
	MCS 0	-87 dBm	-93 dBm	-95 dBm	-98 dBm
	MCS 7	-71 dBm	-74 dBm	-76 dBm	-79 dBm
	MCS 8	-87 dBm	-91 dBm	-93 dBm	-96 dBm
	MCS 15	-68 dBm	-72 dBm	-74 dBm	-77 dBm
OTHER	Dynamic Channel Selection (DCS) based on interference detection Dynamic Frequency Selection (DFS) based on radar signature Automatic Transmit Power Control (ATPC) with EIRP limit support				
LATENCY	< 3 msec				
ANTENNA	QB-8200-EPA	Three N-type Connectors with built-in Surge Protection			
	QB-8250-EPR	Integrated 2x2 MIMO 23dBi Dual Polarized Antenna			
MANAGEMENT					
LOCAL	RS-232 serial (RJ11 to DB-9 dongle provided)				
REMOTE	Telnet and SSH, Web GUI and SSL, TFTP, SNMPv3				
SNMP	SNMP v1-v2c-v3, RFC-1213, RFC-1215, RFC-2790, RFC-2571, RFC-3412, RFC-3414, Private MIB				
OTHER	Syslog, sFlow™ agent, SNTP and local time, Spectrum analyzer				
SECURITY					
ENCRYPTION	AES-CCM 128 bits				
AUTHENTICATION	Internal MAC Address Control List, Radius based Authentication				
NETWORK					
MODES	Bridging (support LACP through external switches), Routing (RIP v2 and IP tunneling)				
IP STACK	IPv4 and IPv6 simultaneously				
THROUGHPUT	Up to 246 Mbps				
GATEWAY FEATURES	DHCP Server & relay, NAT with Std ALGs				
QoS	Asymmetric Bandwidth Control	UL and DL CIR Control "committed information rate" per service flow UL and DL MIR Control "maximum information rate" per service flow			
	Packet Classification Capabilities	802.1D/802.1Q/802.1p priority, IPTOS, VLAN ID, IP source/destination address, source/destination port, Ethernet source/destination address, IP protocol, and Ethertype			
	Scheduling	Best Effort, Real Time Polling Services			
VLAN	802.1Q: Management VLAN. Transparent, Access, Trunk and Mixed mode. QinQ double tagging				
POWER CONSUMPTION	12 Watt typical (22 Watt max)				
ENVIRONMENTAL SPECS					
OPERATING TEMPERATURE	-40° to 60°C (-40° to 140° Fahrenheit) Will continue operating if temperature temporarily varies between -50° and 70°C (-58° and 158° Fahrenheit).				
STORAGE TEMPERATURE	-55° to 80°C (-67° to 176° Fahrenheit)				
HUMIDITY - IP RATING	100% relative humidity - IP67				
WIND LOADING	200 km/h (125 mph)				
PHYSICAL SPECS					
PACKAGED	QB-8200-EPA	14.56 x 13.69 x 8.18 in. (370 x 348 x 208 mm)		15 lbs (6.8 kg)	
	QB-8250-EPR	15.94 x 15.94 x 9.21 in. (405 x 405 x 234 mm)		16.31 lbs (7.4 kg)	
UNPACKAGED	QB-8200-EPA	10.79 x 11.14 x 3.38 in (274 x 283 x 86 mm)		7.7 lbs (3.5 kg)	
	QB-8250-EPR	14.17 x 14.17 x 3.70 in (370 x 370 x 94 mm)		9.0 lbs (4.1 kg)	
SAFETY STANDARDS	UL 60950, CAN/CSA-C22.2 No. 60950, IEC 60950, EN 60950 (part -1 and -22)				
PACKAGE CONTENTS	<ul style="list-style-type: none"> ■ One Tsunami® QB-8200-LNK based on two QB-8200-EPA with three N-type surge protected connectors or One Tsunami® QB-8250-LNK based on two QB-8250-EPR with an integrated 23dBi dual polarized panel antenna ■ Two power injector and country specific power cord ■ Two Wall / Pole mounting kit ■ Two Connector weatherproofing kit (Includes all recommended weatherproofing material) ■ Two Serial (RJ-11 to DB9) dongle ■ Two Grounding kit ■ Two Gigabit PoE Surge Arrestor ■ One Quick Installation Guide 				
MTBF & WARRANTY	>250,000 hours & 1-year on parts and labor; ServPak Extended Support available.				

APPLICATIONS

• Backhaul to a Central POP

Avoid expensive installation and recurring charge of a second wire line backhaul to a remote virtual POP

• Leased Line Redundancy

Eliminate recurring DS-3 leased line charges with one time installation charge of a QuickBridge link

• Repeater

Extend distance or overcome path blockage by adding point-to-point hops

• High-bandwidth Last Mile Access

Use QuickBridge to deliver TLS (Transparent LAN Services) to corporate parks

• Inter-POP Redundancy

Avoid downtimes caused by a wireline backhaul failure by adding a QuickBridge link as an inter-POP redundancy

For detailed technical specifications, please go to <http://www.proxim.com/products/point-to-point-backhaul/tsunami-qb-8200-series>