






MODEL # VZ-215D2iP	
DISPLAY	
Screen Size	21.5"
Max. Resolution	1920 x 1080 @60 Hz pixel
Pixel Pitch	0.248 mm x 0.248 mm
Brightness	250cd/m²(Typical)
Contrast Ratio	1000 : 1
Aspect Ratio	16 : 9
Viewing Angle (H/V)	170° / 160°
Display Color	16.7 Million
Response Time	< 5 ms
Frequency (H)	31 ~ 80Khz
Frequency (V)	56 ~ 75Hz
INTERFACE	
Ethernet 10/100	1
HDMI In	1
WEIGHT & DIMENSIONS	
Outline Dimension (W x H x D) (inch)	20.28 x 15.375 x 7.25
(W x H x D) (mm)	515 x 390 x 184
Net Weight	4.3 Kg / 9.47 lbs
MOUNT	
VESA	100 mm x 100 mm / M4 x 10 mm
GENERAL	
Transmitter - IR Remote Control	Yes
Power - Electrical Ratings	DC 12V, 0.5A(AC100 ~ 240V[50/60Hz])
Warranty - Parts / Labor	3 Year / 3 Year
- MTBF (Approx.)	50,000 Hours
Operating Temperature	32 - 140°F / 0 - 60°C
Multi-lingual Language	English, French, Deutsch, Italian, Spanish, Portuguese, Netherlander
Compatible Mounts - WALL	VZ-WM05, VZ-WM11, VZ-AM01
- RACK	VZ-RMK 08

VZ-215D2iP ADVANTAGES

- 21.5" LED "A" Grade Panel for Commercial Use
- Full HD 1080p Resolution
- Ethernet 10/100
- ONVIF™ Profile S Compliant
- Connects like a camera to your network



INTERFACE



1. DC 12 V In
2. HDMI In
3. ETHERNET 10/100

Contact ViewZ

- Address : 177 W. Orangethorpe Ave., Placentia, CA 92870
- Phone : (714) 996-1177, Fax : (714) 996-1138
- Sales : sales@viewzusa.com
- Specification subject to change without notice.