





VZ-PVM-I2B3 ADVANTAGES:

- 23" Public View Monitor
- Commercial grade LED
- Built in 2.1 Mega Pixel Camera
- Camera Motion Sensor
- Support dual voltage solution (110V AC and 24V DC)
- 3D Comb-filter, De-interlace
- 3-Year Warranty

MODEL #	VZ-PVM-I2B3	
DISPLAY		
Screen Size	23"	
Max. Resolution	1920x1080 @60Hz	
Pixel Pitch	0.265mm x 0.265mm	
Brightness	250cd/m ² (Typical)	
Contrast Ratio	1000:1	
Aspect Ratio	16:9	
Viewing Angle (H/V)	160°/160°	
Display Color	16.7 Million	
Response Time	<5ms	
Video System	NTSC / PAL	
Frequency (H/V)	31~80KHz / 56~75Hz	
INTERFACE		
AV(Composite) In/ Out	1 / 1	
Camera Out	1	
DVI-In / HDMI In / RGB In(15Pin D-Sub)	1 / 1 / 1	
PC Stereo In/Speak Out	1 / 1	
SPECIAL FEATURES		
Multi Display Function	PIP / PBP / VOV	
Filter Type	3D Comb-filter, De-interlace	
Video Resolution(Max)	600 TV Line	
Multi-lingual Language	English, French, Deutsch, Italian, Spanish, Portuguese, Nederland	
DIMENSIONS		
Outline Dimension	21.25" x 16.18" x 3.27"	
(W x H x D)	(539.8mm x 411mm x 83mm)	
Net Weight	21.67 lbs (9.83kg)	
MOUNT		
VESA	200mm x 200mm, M6x8 Screws	
CAMERA		
Camera Type	Mega Pixel IP Camera	
Image Sensor	Panasonic 2.1 Mega Pixel C-MOS Sensor	
Lens	DC Auto Iris 3.6~16mm Vari-focal Lens	
Total / Effect Pixel	1920(H) x 1080p(V) 30p	
Video Compression	H.264 CBR, VBR support	
Video Out	1ch CVBS (NTSC/PAL) RJ-45 1ch output	
Motion Detection	Support	
Interface Ethernet	10/100Base-T	
Webclient Connection Protocol	TCP/IP	
Support Protocol	IPv4, TCP/IP, ARP, HTTP, SMTP, FTP, DHCP, RTP, RTSP, PPPoE	
Function	2D/3DNR, FRC, D-ZOOM, DPC, CLSC, HLC/BLC, Defog	
MEDIA CARD		
Support Type	Photo, Music, Video	
Support File Format	MPEG1, MPEG4, JPEG, BMP, GIF, PNG, MP3	
Memory - Internal	512MB Nand Flash	
- External	USB & SD(4in1)	
Resolution	720 x 576 @60Hz	
GENERAL		
Transmitter - IR Remote Control	YES	
Power - Electrical Ratings	110V AC (50/60Hz)	24V DC
- Consumption	0.5 A (50W)	2.0 A (50W)
Warranty - Parts/ Labor	3 Year / 3 Year	
- MTBF (Approx.)	30,000 Hours	
Operating Temperature	32 - 104°F / 0 - 40°C	
Regulations	TUV-NRTL (=UL), FCC(A)	
Compatible Mounts - WALL	VZ-WM05, VZ-WM11, VZ-AM01	
- CEILING	VZ-CMK01, VZ-CMK02	



INTERFACE



1. HDMI2 IN
2. HDMI1 IN
3. VGA IN
4. DVI IN
5. PC STEREO IN/AUDIO OUT
6. CAMERA OUT
7. AV(composite)2 IN/OUT
8. IP CAMERA ETHERNET
9. MEDIA CARD(USB, SD) - Optional
10. DC 24V IN
11. AC110V IN

Contact ViewZ

- Address: 177 W. Orangethorpe Ave., Placentia, CA 92870
- Phone: (714)996-1177, Fax: (714)996-1138
- Sales: sales@viewzusa.com
- Specifications subject to change without notice.