

# D1255 Series VFD Keypads

www.boschsecurity.com



**BOSCH**

Invented for life



- ▶ Easy to read vacuum fluorescent display (VFD)
- ▶ Easy system control with menu keys
- ▶ User controlled brightness and volume
- ▶ Installer configured menus, text, and custom functions
- ▶ Multiple or single area configurations

Each D1255 Series VFD Keypad model is an SDI bus compatible device that works with the G Series Control Panels and the D9124 Addressable Fire Alarm Panel. Each keypad model has an illuminated keypad, 16-character English language vacuum fluorescent display (VFD), and a sounder that emits eight tones.

## System overview

Use D1255 Series Keypad models in applications for system controllers and annunciators:

- For commercial use, install the keypad in building entrances and areas with unrestricted access. Mounting a keypad near exterior doors in hotel or business lobbies allows people to identify the type and location of the emergency.
- For residential use, install the keypad near the front and rear entrances to the home. Install additional keypads in a kitchen or in a bedroom.
- Use multiple keypads in a large building with many separate areas of security. Program multiple keypads to control multiple areas.
- Install the keypad in locations that are hidden from view. Audible tones from the keypad sounder alert personnel to fire events and assist fire fighters in locating the keypad.

## Functions

### Display

Every D1255 Series Keypad model uses words, numbers, and symbols to show the status of the security system. When several events occur, each model shows each event in order of priority.

### Keys

Each D1255 Series Keypad model has 10 numeric keys and five function keys. Use the [COMMAND] key with the numeric keys to perform a function. Use the [ENT] key or [YES] key to enter your passcode. When pressed, each key emits light and a muted beep.

### Audible Tones

The sounder emits eight distinct warning tones. You can adjust the volume or use a passcode to silence the tone. The tones include:

- Burglary Signal: Steady high-pitched bell tone during alarm.
- Fire Signal: Pulsed high-pitched bell tone during fire alarm.
- Entrance Warning: Intermittent beep tones during entry delay periods.
- Exit Warning: Intermittent beep tones during exit delay periods.

- Invalid Key Buzz: Buzz tone when an invalid key is pressed.
- Keypad Encoding Tone: Muted beep tone as each key is pressed.
- Trouble Buzzer: Two-tone warble during a trouble event.
- Watch Tone: Intermittent beep tone when a watch point is faulted.

### Certifications and approvals

Region	Certification	
USA	UL	D1255: AMCX: Central Station Alarm Units (UL1610, UL1635), AMCX7: Central Station Alarm Units Certified for Canada (cULus), AMTB: Control Panels, SIA False Alarm Reduction, AOTX: Local Alarm Units (UL464, UL609), AOTX7: Local Alarm Units Certified for Canada (cULus), APAW: Police Station Alarm Units (UL365, UL464), APAW7: Police Station Alarm Units Certified for Canada (cULus), APOU: Proprietary Alarm Units (UL1076), APOU7: Proprietary Alarm Units Certified for Canada (cULus), NBSX: Household Burglar Alarm System Units (UL1023), NBSX7: Household Burglar Alarm System Units Certified for Canada (cULus), UTOU: Control Units and Accessories - Household System Type (UL985), UTOU7: Control Units and Accessories - Household System Type Certified for Canada (cULus)
	UL	D1255W: AMCX: Central Station Alarm Units (UL1610, UL1635), AMTB: Control Panels, SIA False Alarm Reduction, AOTX: Local Alarm Units (UL464, UL609), APAW: Police Station Alarm Units (UL365, UL464), APOU: Proprietary Alarm Units (UL1076), NBSX: Household Burglar Alarm System Units (UL1023), UTOU: Control Units and Accessories - Household System Type (UL985)
	FM	D1255
	CSFM	D1255 and D1255W: 7167-1615:0113 FIRE ALARM CONTROL UNIT (COMMERCIAL)
	CSFM	D1255 and D1255W: 7167-1615:0100 CONTROL UNIT (HOUSEHOLD)
	CSFM	7167-1615:0243 7167 -- CONTROL UNIT (HOUSEHOLD)
	CSFM	7165-1615:0119 7165 -- FIRE ALARM CONTROL UNIT (COMMERCIAL)
	NYC-MEA	D1255: 12-92-E, Vol. IV 12-92-E, Vol. IV
	NYC-MEA	D1255: 12-92-E, Vol. 12 12-92-E, Vol. 12
	NYC-MEA	D1255: 12-92-E, Vol. 15 12-92-E, Vol. 15
Canada	ULC	D1255B: AMCX7: Central Station Alarm Units Certified for Canada (cUL), AOTX7: Local Alarm Units Certified for Canada (cUL), APAW7: Police Station

Region	Certification	
		Alarm Units Certified for Canada (cUL), APOU7: Proprietary Alarm Units Certified for Canada (cUL), NBSX7: Household Burglar Alarm System Units Certified for Canada (cUL), UTOU7: Control Units and Accessories - Household System Type Certified for Canada (cUL)
	ULC	AMCX7.S1871 - Central Station Alarm Units Certified for Canada
	ULC	APOU7.S1871 Proprietary Alarm Units Certified for Canada
	ULC	AOTX7.S1871 Local Alarm Units Certified for Canada
	ULC	APAW7.S1871 Police-station-connected Alarm Units Certified for Canada
	ULC	NBSX7.S1871 Household Burglar Alarm System Units Certified for Canada
	ULC	AMCX.S1871, AMCX7.S1871, AMTB.S1871, AOTX.S1871, AOTX7.S1871, APAW.S1871, APAW7.S1871, APOU.S1871, APOU7.S1871, NBSX.S1871, NBSX7.S1871, UTOU.S1871, [D1255 VFD]

### Installation/configuration notes

#### Compatibility Information

<b>Control Panels with SDI Bus</b>	All G Series control panels D9412, D7412, D7212, D9112, and D9124
------------------------------------	--

#### Mounting Considerations

- Do not mount any of the D1255 Series Keypad models in a location exposed to direct sunlight. Direct sunlight can interfere with screen visibility and damage internal components.
- Do not mount any of the D1255 Series Keypad models in damp locations.

#### Power Supplies

A compatible control panel supplies the power and data requirements to a D1255 Series Keypad model through a four-wire connection.

#### Wiring Considerations

Use 0.8 mm (22 AWG) or 1.2 mm (18 AWG) wire. Resistance cannot exceed 25 Ω. Each D1255 Series Keypad model includes a wiring assembly of four color-coded flying leads and one female four-pin connector.

### Parts included

Quant.	Component
1	Keypad

- 1 Hardware pack (3 screws and 3 anchors)
- 1 Literature pack
  - Pull-up Reference Card
  - Users Guide
  - Installation Guide

## Technical specifications

### Connections

Connections:	4-wire flying lead for data and power
Resistance:	25 $\Omega$ maximum

### Environmental Considerations

Temperature (Operating):	0°C to +50°C (+32°F to +122°F)
Relative Humidity:	5% to 85% at +30°C (+86°F)

### Keypad

Dimensions for D1255, D1255W, and D1255R:	11.7 cm x 21 cm x 2 cm (4.6 in. x 8.2 in. x 0.8 in.)
Dimensions for D1255B:	12.6 cm x 20 cm x 3.2 cm (5 in. x 7.9 in. x 1.3 in.)
Weight for All Models:	439 g (15.5 oz)
Material for All Models:	CHI MEI POLYLAC PA757 ABS with UV Stabilizer. UL94-HB Fire Rated
Display Window:	16-character vacuum fluorescent display Each character is a 14-segment unit
Indicators:	Illuminated keys Warning and indicating tones

### Number of...

D1255 Series Keypad Models per Control Panel:	Eight supervised 32 unsupervised
---	----------------------------------

### Power Requirements

Voltage:	Nominal 12 VDC
Current:	Idle 104 mA, armed or disarmed; Maximum 206 mA, with keypad lit and warning tone on

### Trademarks

Trademark names are used throughout this document. In most cases, these designations are claimed as trademarks or registered trademarks in one or more countries by their respective owners. Rather than placing a trademark symbol in every occurrence of a trademark name, Bosch Security Systems, Inc. uses the names only in an editorial fashion and to the benefit of the trademark owner with no intention of infringing the trademark.

POLYLAC is a registered trademark of CHI MEI Industrial Corporation, LTD.

Plexiglas is a registered trademark of Arkema.

## Ordering information

### D1255 VFD Keypad

Off-white classic case.  
Order number **D1255**

### D1255W VFD Keypad

White classic case.  
Order number **D1255W**

### D1255R VFD Keypad

Red classic case.  
Order number **D1255R**

### D58A Fire Alarm Kit

Red overlays and reference sheets for D720R Keypads in fire alarm applications.  
Order number **D58A**

### D1255B VFD Keypad

White and gray modern case.  
Order number **D1255B**

### Accessories

#### D54B Brass Flush-mount Kit

Back box and polished brass faceplate.  
Order number **D54B**

#### D54C Stainless Steel Flush-mount Kit

Back box and stainless steel faceplate.  
Order number **D54C**

#### D55 Keypad Desk Stand

Portable desk stand in smoke colored Plexiglas.  
Order number **D55**

#### D56 Surface Mount Conduit Box

White surface mount box.  
Order number **D56**

#### D56R Red Surface Mount Conduit Box

Red surface mount box.  
Order number **D56R**

**Represented by:**

**Americas:**

Bosch Security Systems, Inc.  
130 Perinton Parkway  
Fairport, New York, 14450, USA  
Phone: +1 800 289 0096  
Fax: +1 585 223 9180  
security.sales@us.bosch.com  
www.boschsecurity.us

**Europe, Middle East, Africa:**

Bosch Security Systems B.V.  
P.O. Box 80002  
5617 BA Eindhoven, The Netherlands  
Phone: + 31 40 2577 284  
Fax: +31 40 2577 330  
emea.securitysystems@bosch.com  
www.boschsecurity.com

**Asia-Pacific:**

Robert Bosch (SEA) Pte Ltd, Security  
Systems  
11 Bishan Street 21  
Singapore 573943  
Phone: +65 6571 2808  
Fax: +65 6571 2699  
apr.securitysystems@bosch.com  
www.boschsecurity.asia

**China:**

Bosch (Shanghai) Security Systems Ltd.  
201 Building, No. 333 Fuquan Road  
North IBP  
Changning District, Shanghai  
200335 China  
Phone +86 21 22181111  
Fax: +86 21 22182398  
www.boschsecurity.com.cn

**America Latina:**

Robert Bosch Ltda Security Systems Division  
Via Anhanguera, Km 98  
CEP 13065-900  
Campinas, Sao Paulo, Brazil  
Phone: +55 19 2103 2860  
Fax: +55 19 2103 2862  
latam.boschsecurity@bosch.com  
www.boschsecurity.com