

VDC-480 Series Dome Cameras FlexiDome XF Indoor

www.boschsecurity.com



BOSCH
Invented for life



- ▶ Indoor polycarbonate dome
- ▶ XF-Dynamic for wide dynamic range
- ▶ NightSense
- ▶ 15-bit DSP technology
- ▶ 540 TVL color resolution

The FlexiDome^{XF} Indoor series are the ultimate solutions for virtually any indoor surveillance application. These units contain full-featured color cameras, with a 1/3-inch CCD and integral varifocal lenses.

Installation is quick and easy, since the cameras come completely assembled and ready to use. Using the proprietary pan/tilt/rotation mechanism, installers can select the exact field of view. Mounting options are numerous, including surface, 4S (USA), wall, corner, and suspended ceiling.

The VDC-480 series dome cameras are an ideal solution for many surveillance applications, especially where backlighting may be a concern. Their compact, sleek design and virtually flush-mount appearance will complement any decor.

Functions

Technology

The VDC-480 series incorporates the latest technology adopted from the high-performance Dinion^{XF} Color cameras. This technology ensures the highest possible image quality at all times and under all conditions. Based on a unique combination of 15-bit digital video processing and XF-dynamic, these cameras provide

excellent sensitivity, with up to 32 x extended dynamic range. This delivers a sharper, more detailed image with outstanding accuracy in color reproduction.

Operation

All cameras feature video motion detection, auto black, default shutter, and back light compensation for optimum performance in all lighting conditions. The lens wizard and focus aid make lens adjustment easy and straightforward, and ensure proper focus throughout the 24-hour cycle. All cameras incorporate Bilinx, a technology that allows technicians to set up, control the camera settings, and even update firmware remotely over the video cable.

Controls and Indicators

- OSD
- 5-key operation

Interconnections


- Video connection BNC on flying lead
- Power connection on flying leads

Certifications and approvals

Safety	UL 1950; CSA 22.2 No. 950; EN 60950 (CE)
Immunity	EN 50130-4 (CE)
Emission	EN 50022 class B (CE); FCC, class B part 15

Region	Certification	
Europe	CE	Declaration of Conformity
USA	FCC	Declaration of Conformity

Installation/configuration notes




1	C-480	Color (with NightSense)
2	03	3 to 9.5 mm F1.0
	04	3.7 to 12 mm F1.6
	09	9 to 22 mm F1.4
3	10	PAL color or CCIR mono
	20	NTSC color or EIA mono
4		Flush mount
	S	Surface mount

Model overview


Model	Standard	Lens
VDC-480V03-10	PAL	3 to 9.5 mm F1.0
VDC-480V03-20	NTSC	3 to 9.5 mm F1.0
VDC-480V04-10	PAL	3.7 to 12 mm F1.6
VDC-480V04-20	NTSC	3.7 to 12 mm F1.6
VDC-480V09-10	PAL	9 to 22 mm F1.4
VDC-480V09-20	NTSC	9 to 22 mm F1.4

BNC to UTP Transceiver




mm (in)

Indoor Flush Mounting




mm (in)

VDA-445SMB-Surface Mount Box




mm (in)


VDA-WMT-DOME –Pendant Wall Mount



VDA-PMT-DOME –Pendant Pipe Mount



VDA-CMT-DOME –Corner Mount



Technical specifications

Electrical

Power supply	
Rated voltage	12 VDC or 24 VAC, 50/60 Hz
Voltage range	10.8 to 39 VDC or 12 to 28 VAC, 45 to 65 Hz
Power consumption	4 W
Imager	Interline transfer CCD, 1/3-inch image format
Active picture elements	
PAL models	752 H x 582 V
NTSC models	768 H x 494 V

Sensitivity (3200 K)

Model	Usable picture	Usable picture	Full video
	(30 IRE)	(50 IRE)	(100 IRE)

Color

VDC-480V03	Color	0.16 lx (0.015 fc)	0.35 lx (0.033 fc)	1.4 lx (0.13 fc)
	Color + 10 x SensUp	0.016 lx (0.0015 fc)	0.035 lx (0.0033 fc)	0.14 lx (0.013 fc)
	NightSense	0.056 lx (0.0052 fc)	0.13 lx (0.012 fc)	0.5 lx (0.046 fc)
	NightSense + 10 x SensUp	0.0056 lx (0.00052 fc)	0.013 lx (0.0012 fc)	0.05 lx (0.0046 fc)

VDC-480V04	Color	0.4 lx (0.037 fc)	0.9 (0.083)	3.6 (0.33)
	Color + 10 x SensUp	0.04 lx (0.0037 f c)	0.09 (0.0083)	0.36 (0.033)
	NightSense	0.14 lx (0.013 fc)	0.32 (0.03)	1.3 (0.12)
	NightSense + 10x SensUp	0.014 lx (0.0013 f c)	0.032 (0.003)	0.13 (0.012)
VDC-480V09	Color	0.28 lx (0.027 fc)	0.62 lx (0.058 f c)	2.48 lx (0.23 fc)
	Color + 10 x SensUp	0.028 lx (0.0027 f c)	0.062 lx (0.0058)	0.248 lx (0.023 f c)
	NightSense	0.099 lx (0.0092 f c)	0.23 lx (0.021)	0.88 lx (0.081)
	NightSense + 10 x SensUp	0.0099 lx (0.00092)	0.023 lx (0.0021)	0.088 lx (0.0081)

SensUp	Automatic continuous up to 10 x, off selectable
Horizontal resolution	540 TVL
Signal-to-noise ratio	>50 dB
AGC	Auto, maximum level selectable 28 dB
Auto black	On/off selectable
Electronic shutter	Flickerless, on/off, default shutter
NightSense	Auto, forced, off selectable
Dynamic range	32 x dynamic range enhancement
Dynamic noise reduction	Automatic, off, selectable
Sharpness correction	Horizontal and vertical, symmetrical
Backlight compensation	Off, programmable window and level selectable
White balance	Automatic sensing (2500 to 9000 K), AWB hold and manual
Video motion detector	Four (4) areas, sensitivity selectable
Camera ID	16-character editable string, position selectable
Video output	Composite video 1.0 Vpp, 75 ohm
Remote control	Bi-directional coaxial communication
Synchronization	Internal or LineLock*
Connector	Flying leads (through the back)

* LineLock (only when AC-powered) synchronizes the camera to the power line zero crossing for roll-free vertical interval switching. Vertical phase delay can be adjusted (from 0° to 358°) to allow vertical synchronization in multi-phase power installations.

Optical

Varifocal	Manual zoom and focus adjustment
Iris control	Automatic iris control
Viewing angle	
3 to 9.5 mm	Wide 95° x 69° (H x V) Tele 30.2° x 22.6° (H x V)
3.7 to 12 mm	Wide 76.1° x 55.8° (H x V) Tele 23.8° x 17.9° (H x V)
9 to 22 mm	Wide: 31.2° x 22.8° (H x V) Tele: 12.8° x 9.6° (H x V)

Mechanical

Dimensions	See drawings
Weight	740 g (1.63 lb)
Mounting	Flush on hollow surface with three (3) screws in a 4S electrical box
Color	White (RAL9010) trim ring with black inner liner
Adjustment range	360° pan, 90° tilt, ±90° azimuth
Dome bubble	Polycarbonate, clear with UV blocking anti-scratch coating
Trim ring	Polycarbonate

Environmental

Operating temperature	-10 °C to +45 °C (-14 °F to +113 °F)
Storage temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Humidity	5% to 93% relative humidity

Ordering information

VDC-480V03-10 Indoor Color Model

1/3-inch, PAL color, 540 TVL, 12 VDC/24 VAC, 50 Hz, w/3-9.5 mm F1.0 Varifocal lens, white
Order number **VDC-480V03-10**

VDC-480V03-10S Indoor Color Model, Surface mount

1/3-inch, PAL color, 540 TVL, 12 VDC/24 VAC, 50 Hz, w/3-9.5 mm F1.0 Varifocal lens, white, surface mount
Order number **VDC-480V03-10S**

VDC-480V03-20 Indoor Color Model

1/3-inch, NTSC color, 540 TVL, 12 VDC/24 VAC, 60 Hz, w/3-9.5 mm F1.0 Varifocal lens, white
Order number **VDC-480V03-20**

VDC-480V03-20S Indoor Color Model, Surface mount

1/3-inch, NTSC color, 540 TVL, 12 VDC/24 VAC, 60 Hz,
w/3-9.5 mm F1.0 Varifocal lens, white, surface mount
Order number **VDC-480V03-20S**

VDC-480V04-10 Indoor Color Model

1/3-inch, PAL color, 540 TVL, 12 VDC/24 VAC, 50 Hz,
w/3.7-12 mm F1.0 Varifocal lens, white
Order number **VDC-480V04-10**

VDC-480V04-10S Indoor Color Model, Surface mount

1/3-inch, PAL color, 540 TVL, 12 VDC/24 VAC, 50 Hz,
w/3.7-12 mm F1.0 Varifocal lens, white, surface mount
Order number **VDC-480V04-10S**

VDC-480V04-20 Indoor Color Model

1/3-inch, NTSC color, 540 TVL, 12 VDC/24 VAC, 50 Hz,
w/3.7-12 mm F1.0 Varifocal lens, white
Order number **VDC-480V04-20**

VDC-480V04-20S Indoor Color Model, Surface mount

1/3-inch, NTSC color, 540 TVL, 12 VDC/24 VAC, 50 Hz,
w/3.7-12 mm F1.0 Varifocal lens, white, surface mount
Order number **VDC-480V04-20S**

VDC-480V09-10 Indoor Color Model

1/3-inch, PAL color, 540 TVL, 12 VDC/24 VAC, 50 Hz,
w/9-22 mm F1.0 Varifocal lens, white
Order number **VDC-480V09-10**

VDC-480V09-10S Indoor Color Model, Surface mount

1/3-inch, PAL color, 540 TVL, 12 VDC/24 VAC, 50 Hz,
w/9-22 mm F1.0 Varifocal lens, white, surface mount
Order number **VDC-480V09-10S**

VDC-480V09-20 Indoor Color Model

1/3-inch, NTSC color, 540 TVL, 12 VDC/24 VAC, 50 Hz,
w/9-22 mm F1.0 Varifocal lens, white
Order number **VDC-480V09-20**

VDC-480V09-20S Indoor Color Model, Surface mount

1/3-inch, NTSC color, 540 TVL, 12 VDC/24 VAC, 50 Hz,
w/9-22 mm F1.0 Varifocal lens, white, surface mount
Order number **VDC-480V09-20S**

Accessories**VDA-445SMB**

Surface mount box, indoor for VDM-345 and VDC-445
Order number **VDA-445SMB**

VDA-455UTP

Adaptor for UTP twisted pair output
Order number **VDA-455UTP**

VDA-455TBL Tinted bubble

Tinted bubble for FlexiDome series
Order number **VDA-455TBL**

VDA-455CBL Clear bubble

Clear Bubble for FlexiDome series
Order number **VDA-455CBL**

S1460 Service/Monitor Cable

for FlexiDome analog and IP (2.5 mm connector to BNC), 1 m
Order number **S1460**

UPA-1509-60 Power Supply

120 VAC, 60 Hz, 15 VDC, 9 VA Out
Order number **UPA-1509-60**

UPA-1509-50 Power Supply

220 VAC, 50 Hz, 15 VDC, 9 VA Out
Order number **UPA-1509-50**

UPA-2420-50 Power Supply

220 VAC, 50 Hz, 24 VAC, 20 VA Out
Order number **UPA-2420-50**

UPA-2450-50 Power Supply, 220 V, 50 Hz

Indoor, 220 VAC, 50 Hz In; 24 VAC, 50 VA Out
Order number **UPA-2450-50**

Software Options**VP-CFGSFT Configuration Software**

for cameras using Bilinx, includes VP-USB Adaptor
Order number **VP-CFGSFT**

Represented by:

Americas:

Bosch Security Systems, Inc.
130 Perinton Parkway
Fairport, New York, 14450, USA
Phone: +1 800 289 0096
Fax: +1 585 223 9180
security.sales@us.bosch.com
www.boschsecurity.us

Europe, Middle East, Africa:

Bosch Security Systems B.V.
P.O. Box 80002
5617 BA Eindhoven, The Netherlands
Phone: + 31 40 2577 284
Fax: +31 40 2577 330
emea.securitysystems@bosch.com
www.boschsecurity.com

Asia-Pacific:

Robert Bosch (SEA) Pte Ltd, Security
Systems
11 Bishan Street 21
Singapore 573943
Phone: +65 6571 2808
Fax: +65 6571 2699
apr.securitysystems@bosch.com
www.boschsecurity.asia

China:

Bosch (Shanghai) Security Systems Ltd.
201 Building, No. 333 Fuquan Road
North IBP
Changning District, Shanghai
200335 China
Phone +86 21 22181111
Fax: +86 21 22182398
www.boschsecurity.com.cn

America Latina:

Robert Bosch Ltda Security Systems Division
Via Anhanguera, Km 98
CEP 13065-900
Campinas, Sao Paulo, Brazil
Phone: +55 19 2103 2860
Fax: +55 19 2103 2862
latam.boschsecurity@bosch.com
www.boschsecurity.com