

# HS4-241575W-FW Fixed-candela Horn Strobe (white)

www.boschsecurity.com



**BOSCH**

Invented for life



- ▶ 24 VDC, filtered or FWR
- ▶ Listed at 15 cd, but provides 75 cd on axis
- ▶ Continuous or temporal (Code 3) horn tones
- ▶ Selectable dBA settings (high, medium, or low)
- ▶ Easy wall mounting on a variety of back boxes

This Wheelock horn strobe is UL Listed for indoor wall-mount applications. The strobe is listed at 15 cd, but provide 75 cd on axis. The horn provides a continuous horn tone or temporal (Code 3) horn tone with three selectable sound output (dBA) settings for each tone . The temporal tone can be synchronized by using an SM (single) or DSM (dual) Synchronization Module or a compatible control panel. The strobe and horn circuits can be operated independently.

## Certifications and approvals

Region	Certification	
USA	UL	ULSZ: Audible Signal Appliances (UL464), UUKC: Signaling Appliances and Equipment for the Hearing Impaired (UL1971)
	CSFM	see our website

## Installation/configuration notes

### Compatible Products

The following products are compatible with the HS4 Horn Strobes:

Category	Product ID	Product Description
Control Panels	D7022 <sup>1</sup>	Conventional FACP
	D7024 <sup>2</sup>	Addressable FACP
	D7024	Conventional FACP
	D8024 <sup>1</sup>	Analog FACP
	D9124 <sup>1</sup>	Addressable FACP
	D10024A <sup>1</sup>	Analog FACP
	FPA-1000	Analog Addressable FACP
	FPD-7024 <sup>2</sup>	Addressable FACP
Modules	FPD-7024	Conventional FACP
	SM-12/24-R	Synchronization module (red)
	DSM-12/24-R	Dual synchronization module (red)

<sup>1</sup> For synchronization, use the SM or DSM Synchronization Modules. The synchronization module must be set for 24 VDC operation. When used, the D7022 must be set for 24 VDC operation.

<sup>2</sup> When used with a D7039 Multiplex Expansion Module, the D7024 and FPD-7024 become addressable fire alarm control panels (FACPs).

### Mounting Considerations

#### Indoor Applications

Mount these HS4 Horn Strobes on the indicated back boxes for the indicated applications:

	Conduit Applications	Surface Mounted	Flush Mounted
Double-gang			•
Four-inch square			•
100-mm European			•
IOB <sup>1</sup>	•	•	
SHBB-R	•	•	

<sup>1</sup> Although the IOB Back Box is an indoor or outdoor box, the HS4 Series Horn Strobes are only UL Listed for indoor applications.

### Wiring

#### Notice

The horn circuit of these horn strobes can be used on coded systems where the applied voltage is cycled on and off, but the strobe circuit cannot.

The input terminals accept wires with diameters between 18 AWG and 12 AWG (ISO 0.75 mm<sup>2</sup> and 4 mm<sup>2</sup>).

### Parts included

Quant.	Component
1	Horn strobe
1	Hardware pack
1	Literature pack

### Technical specifications

#### Electrical

Current (maximum) VDC

Audible only:	High dBA: 110 mA Medium dBA: 68 mA Low dBA: 27 mA
---------------	---

Strobe only:	15 cd: 60 mA 30 cd: 92 mA 75 cd: 165 mA 110 cd: 220 mA
--------------	---

Current (maximum) VFWR

Audible only:	High dBA: 94 mA Medium dBA: 50 mA Low dBA: 41 mA
---------------	--

Strobe only:	15 cd: 102 mA 30 cd: 155 mA 75 cd: 253 mA 110 cd: 347 mA
Voltage (input)	24 VDC nominal filtered or FWR; 16 VDC to 33 VDC

### Environmental

Relative Humidity:	Up to 95%, non-condensing
Temperature (Operating):	+32°F to +120°F (0°C to +49°C)

### Mechanical

Candela Selections:	15 cd, 30 cd, 75 cd, or 110 cd
Dimensions (H x W x D):	4.125 in. x 4.125 in. x 1.25 in. (10.5 cm x 10.5 cm x 3.2 cm)
Material:	Molded plastic enclosure incorporating a Xenon flashtube and Lexan lens

### Horn Ratings at 24 VDC

#### Continuous Horn

Reverberant dBA at 10 ft (3 m) per UL464:	High: 91 dBA Medium: 88 dBA Low: 83 dBA
---	---

#### Temporal (Code 3) Horn

Reverberant dBA at 10 ft (3 m) per UL464:	High: 87 dBA Medium: 84 dBA Low: 79 dBA
---	---

#### Notice

The sound output for the Temporal (Code 3) mode is rated lower than in Continuous mode because the time that the horn is off is averaged into the sound output rating. When the horn produces a tone in Temporal mode, its sound pressure is the same as the Continuous mode.

### Trademarks

All hardware and software product names used in this document are likely to be registered trademarks and must be treated accordingly.

### Ordering information

#### HS4-241575W-FW Fixed-candela Horn Strobe (white)

This white horn strobe is UL Listed for indoor wall-mount use at 15 cd (75 cd on axis) and temporal (Code 3) or continuous horn tone with three selectable sound output (dBA) settings for each tone. Synchronize the temporal code using an SM (single) or DSM (dual) module or a compatible control panel. Order number **HS4-241575W-FW**

**Represented by:**

**Americas:**

Bosch Security Systems, Inc.  
130 Perinton Parkway  
Fairport, New York, 14450, USA  
Phone: +1 800 289 0096  
Fax: +1 585 223 9180  
security.sales@us.bosch.com  
www.boschsecurity.us

**Europe, Middle East, Africa:**

Bosch Security Systems B.V.  
P.O. Box 80002  
5617 BA Eindhoven, The Netherlands  
Phone: + 31 40 2577 284  
Fax: +31 40 2577 330  
emea.securitysystems@bosch.com  
www.boschsecurity.com

**Asia-Pacific:**

Robert Bosch (SEA) Pte Ltd, Security  
Systems  
11 Bishan Street 21  
Singapore 573943  
Phone: +65 6571 2808  
Fax: +65 6571 2699  
apr.securitysystems@bosch.com  
www.boschsecurity.asia

**China:**

Bosch (Shanghai) Security Systems Ltd.  
201 Building, No. 333 Fuquan Road  
North IBP  
Changning District, Shanghai  
200335 China  
Phone +86 21 22181111  
Fax: +86 21 22182398  
www.boschsecurity.com.cn

**America Latina:**

Robert Bosch Ltda Security Systems Division  
Via Anhanguera, Km 98  
CEP 13065-900  
Campinas, Sao Paulo, Brazil  
Phone: +55 19 2103 2860  
Fax: +55 19 2103 2862  
latam.boschsecurity@bosch.com  
www.boschsecurity.com