




Regulatory : 



Cordset : 3 meter 4mm sq H05V V-F cable with IEC60309 32A 2P + E plug  
Fuse : 2 x 16A Resettable Fuse  
Input Rating : 32A / 250Vac


For 32A Rating PDU, the models which have 20 socket outlets,  
< CIRCUIT A > Socket #1-8 C13 & #C1-C2 C19 socket outlets can only output 16A maximum.  
< CIRCUIT B > Socket #9-16 C13 & #C3-C4 C19 socket outlets can only output 16A maximum.

Model : V16C13/4C19-20A



Cordset : 3 meter 2.5mm sq H05V V-F cable with 20 Amp open-end  
Fuse : 1 x 20A Resettable Fuse  
Input Rating : 20A / 250Vac

Model : V16C13/4C19-16A



Cordset : 3 meter 1.5mm sq H05V V-F cable with IEC60309 16A 2P + E or IEC320 C20 plug  
Fuse : 1 x 16A Resettable Fuse  
Input Rating : 16A / 250Vac

UNIT : mm

Common Specification :

Description : 16 outlets IEC320 C13, 4 outlets IEC320 C19  
Receptacles : 16 outlets IEC320 C13 10A Rated, 4 outlets IEC320 C19 16A Rated

PDU Dimension : 60 (W) x 50 (D) x 1050 (H) mm  
Packing :

Net Weight :  
Gross Weight :

WARNING : The individual user should take care to determine prior to use whether this device is suitable, adequate or safe for the use intended. Since individual applications are subject to great variation, the manufacturer makes no representation or warranty as to the suitability or fitness of these devices for any specific application.

The company reserves the right to modify product specifications without prior notice and assumes no responsibility for any error which may appear in this publication.

Copyright 2012 Austin Hughes Electronics Ltd. All rights reserved.