


Model : V16UK45-32A_EN/3B-1

EMEA code : AHV163000000303111



Safety Regulatory : **FC** **CE**

Environmental : **RoHS** **REACH**

Cordset : 3 meter 4mm sq H05V V-F cable with IEC60309 32A 2P + E plug
Input Rating : 32A / 250Vac

For 32A Rating PDU, the models which have 16 socket outlets,
< CIRCUIT A > Socket #1-8 UK socket outlets can only output 16A maximum.
< CIRCUIT B > Socket #9-16 UK socket outlets can only output 16A maximum.

Model : V16UK45-20A_OE/3B-1

EMEA code : AHV163000000503511



Cordset : 3 meter 2.5mm sq H05V V-F cable with 20 Amp open-end
Input Rating : 20A / 250Vac

Model : V16UK45-16A_EN/3B-1

EMEA code : AHV163000000203111

OR

V16UK45-16A_C20/3B-1

AHV163000000203211




OR



Cordset : 3 meter 1.5mm sq H05V V-F cable with IEC60309 16A 2P + E or IEC320 C20 plug
Input Rating : 16A / 250Vac

Model : V16UK45-13A_BS/3B-1

EMEA code : AHV163000000103311



Cordset : 3 meter 1.5mm sq H05V V-F cable with 13 Amp BS1363 plug
Input Rating : 13A / 250Vac

UNIT : mm

Common Specification :

Description : 16 outlets UK, 45 degree (left side mounting)
Receptacles : 16 outlets UK BS1363 13A Rated, Angled 45 degree

PDU Dimension : 60 (W) x 50 (D) x 1200 (H) mm
Packing :

Net Weight :
Gross Weight :

WARNING : The individual user should take care to determine prior to use whether this device is suitable, adequate or safe for the use intended. Since individual applications are subject to great variation, the manufacturer makes no representation or warranty as to the suitability or fitness of these devices for any specific application.

The company reserves the right to modify product specifications without prior notice and assumes no responsibility for any error which may appear in this publication.

Copyright 2013 Austin Hughes Electronics Ltd. All rights reserved.