

PANDUIT P/N	WEIGHT
SP688-*	.047 LB/10 PCS (21.4 g/10 PCS)


1. MATERIAL: HOUSING, LOAD BAR, DIVIDER, STRAIN COLLAR - THERMOPLASTIC UL94V-0 RATED; STRAIN RELIEF BOOT - CLEAR PVC; CONTACT TERMINAL - PHOSPHOR BRONZE ELECTRO-POLISHED AND PLATED WITH .000050" MIN. GOLD IN MATING AREA, GOLD FLASH OVER REMAINDER, .000100" MIN. NICKEL UNDERPLATE.

2. PLUG ACCEPTS 4 PAIR CABLE .225-.250" DIA. WITH 24 AWG STRANDED CONDUCTOR WITH A MAXIMUM INSULATOR DIAMETER OF .040".

3. MEETS DIMENSIONAL REQUIREMENTS OF FCC PART 68 AND IEC 60603-7. ALL DIMENSIONS MAXIMUM UNLESS OTHERWISE SPECIFIED.

4. TERMINATED CONTACT HEIGHT DIMENSION: .237±.005".

5. SEE CURRENT CATALOG FOR ADDITIONAL PART NUMBER SUFFIXES TO INDICATE PACKAGE QUANTITY.



2	7-15-03	MIR		C. REMOVED "SOLID" FROM NOTE 2. B. REVISED MATERIAL CALLOUT FOR STRAIN RELIEF BOOT.	01185-15				
1	2-18-03	MDJR	NGM	A. ADDED NOTE 5.	01185-15		PMH		
R	10-15-02	MDJR	NGM	RELEASED TO PRODUCTION	01185-15		PMH		KMCL
REV	DATE	BY	CHK	DESCRIPTION	ECN - R	CUST	SUP	OTH	