

rayLUX 200

DIRECTIONAL WHITE-LIGHT

High Performance White-Light LED illuminators provide class leading performance, long life, energy efficiency and zero maintenance. They incorporate the very latest surface mount LED's to deliver excellent optical output and outstanding reliability, providing even illumination and excellent night time images for surveillance cameras and general area lighting.

The unique Adaptive Illumination™ concept provides the flexibility to alter the angle of illumination on site to suit the required lighting specification. The RAYLUX 200 provides a world class 'White-Light' output of 110lm/W at the LED source, and an independently tested luminaire output of 4700 lm at 80lm/w.

Each unit is fitted with Active LED Life Control to carefully control LED output, delivering consistent illumination power and a projected working life of 10 years.

RAYLUX illuminators are supplied with bracket and power supply. Control features on the power supply include adjustable power output, photocell and telemetry control. RAYLUX 200 is suitable for all low light installations up to 200m (656ft).



POWERFUL

- Quick Start
- **PLATINUM[®]** LED technology
- High Power - Low Running Costs

FLEXIBLE

- Adaptive Illumination™
- Various angles (10° to 180°)
- Fully Controllable Power Supply

RELIABLE

- 10 year life
- Active LED Life Control
- Vandal resistant

CONTROLLED

- Excellent Colour Rendition
- Even Output Illumination
- Low Running Costs

ADAPTIVE ILLUMINATION™:




Narrow Angle



Wide Angle

WHITE-LIGHT IN USE:



White-Light off



White-Light on

Version 3.2

APPLICATIONS



PRISONS



WATER RESERVOIRS



INDUSTRIAL PARK






DOME SYSTEM



POWER PLANTS

rayTEC[®]

TECHNICAL SPECIFICATIONS



ILLUMINATOR

Lumens:	Source 110 per watt lm/w – luminaire 80 lm/w
Total lumens*:	4,700 per luminaire
Max Distance:	up to 200m (656ft)
Angle:	Various - See Part Codes
Optics:	SMT LED's
Consumption:	80W max
Voltage:	14V current controlled
Colour Temperature**:	6500k
Colour Reproduction Index**:	74-80+
Weight:	4kg (8.8lbs)
Environmental:	IP66
Temp Range:	-50 to +50°C (-58 to 122°F)
Cable Length:	2.5m
Colour:	Silver
Wavelength:	White-Light
Dimensions:	280 x 195 x 66mm 11" x 8" x 3" approx

BRACKETRY

U Bracket and Adaptive Illumination bracket included.

POWER SUPPLY

Input:	Universal 100-240V AC auto-sensing
Output:	80W max
Temperature:	-50 to +50°C (-58 to 122°F)
Weight:	1.8kg (4lbs)
Dimensions:	160mm x 160mm x 90mm 6" x 6" x 4" approx

Standard PSU (included)

Adjustable photocell
Adjustable power output for IR
Telemetry Control

Alternative PSU Options include:

PRO and PRO-IQ intelligent range of power supplies with multi function options including remote dimming.

* Lumen output depends upon final lens selection. Lumen output shown based on average between 10 and 50 degree angles.


** Cool White as standard - Warm White options available. CRI published reflects range between Cool and Warm White.

5 YEAR WARRANTY


All Raytec CCTV illuminators are provided with a 5 year warranty, unmatched anywhere in the CCTV lighting industry. Raytec illuminators provide guaranteed long life!



Examples of PHOTOMETRIC DIAGRAMS for RL200 (Full photometry available)



Area 25m x 45m
6m mounting height
RL200-AI-50 shown at a 70° setting



Area 25m x 45m
6m mounting height
RL200-AI-50 shown at a 50° setting

PART CODES & DISTANCES

			NARROW ANGLE	WIDE ANGLE
RL200-AI-10	RAYLUX 200, 10-20°	AI, white-light + PSU	200m (656ft)	140m (459ft)
RL200-AI-30	RAYLUX 200, 30-60°	AI, white-light + PSU	105m (344ft)	74m (241ft)
RL200-AI-50	RAYLUX 200, 50-100°	AI, white-light + PSU	80m (262ft)	56m (184ft)
RL200-AI-120	RAYLUX 200, 120-180°	AI, white-light + PSU	30m (98ft)	21m (69ft)



Europe / Middle East: Tel: +44 (0) 1670 520055
Americas (Toll Free): Tel: +1 888 505 8335

Email: sales@rayteccctv.com
Email: ussales@rayteccctv.com
Web: www.rayteccctv.com