


IR Indoor/Outdoor Bullet Camera

VLEDB1G	2.8-12mm auto iris varifocal lens, dark grey housing
VLEDB1W	2.8-12mm auto iris varifocal lens, white housing
VLEDB2G	3.6mm fixed lens, dark grey housing
VLEDB2W	3.6mm fixed lens, white housing

Features

- 1/3" Panasonic CCD
- 0 lux with 36 IR LEDs built-in (VLEDB1G/VLEDB1W)
0 lux with 24 IR LEDs built-in (VLEDB2G/VLEDB2W)
- 98' IR range (depending on scene reflection) (VLEDB1G/VLEDB1W)
65' IR range (depending on scene reflection) (VLEDB2G/VLEDB2W)
- IP66 compliant
- 2 year warranty

IR



Specifications

Image Sensor	1/3" Panasonic CCD
Resolution.....	600 TV lines
Minimum Illumination.....	0.1 lux, 0 lux with IR on
Effective Pixels	769 (H) x 494 (V)
Number of LEDs.....	VLEDB1G/VLEDB1W: 36 VLEDB2G/VLEDB2W: 24
IR Range	VLEDB1G/VLEDB1W: Up to 98' (depending on scene reflection) VLEDB2G/VLEDB2W: Up to 65' (depending on scene reflection)
IR LED Wavelength	850nm
IR Status.....	IR on: under 10 lux, by CDS auto control
Electronic Shutter	Auto (1/60 sec. - 1/100,000 sec.)
S/N Ratio	More than 48dB
Backlight Compensation..	Auto
White Balance	Auto

AGC.....	Auto
Gamma.....	0.45 typ.
Scanning System.....	2:1 interlace
Synchronization.....	Internal
Video Signal Output.....	1.0Vp-p / 75 ohms
Operating Temperature....	14° F – 122° F
Storage Temperature.....	-4° F – 140° F
Power Consumption	Max. 100mA (IR off) VLEDB1G/VLEDB1W: max. 360mA (IR on) VLEDB2G/VLEDB2W: max. 300mA (IR on)
Power Supply	12VDC (power supply not included)
Dimensions.....	VLEDB1G/VLEDB1W: 3.8 (W) x 3.3 (H) x 9 (L) VLEDB2G/VLEDB2W: 2.75" (W) x 2.5" (H) x 6.7" (L)
Weight	VLEDB1G/VLEDB1W: 1.4 lbs. VLEDB2G/VLEDB2W: 9.6 oz.

Optional Accessory



PSW5
12VDC
Power Supply

Speco Technologies is constantly developing and improving products.
We reserve the right to modify product design and specifications without notice
and without incurring any obligation. Spec Rev. 9/27/13