

Anixter Level 1 for Industrial Network Environments

Industrial Ethernet Cable: Cat 5e 24-4 Pair Solid UTP CMP Blue



L1-5E-S0L-UTP-P-06	CAT5e (200MHz), 4-Pair, U/UTP-Unshielded, Plenum-CMP, Premise Horizontal Cable, 24 AWG Solid Bare Copper Conductors, Dual FRPO/FEP Insulation, Rip Cord, Blue Plenum jacket.
---------------------------	--

Physical Characteristics (Overall)	
Conductor	
# Pairs	4
AWG	24
Stranding	Solid
Material	BC - Bare Copper
Total # of Conductors	8
Insulation	
Material	FRPO/FEP - Flame Retardant Polyolefin/Fluorinated Ethylene Propylene
Outer Shield	
Type	Unshielded
Outer Jacket	
Material	LS PVC - Low Smoke Polyvinyl Chloride
Nominal Diameter	.190 in.
Outer Jacket Rip Cord	Yes

Pair Color Code Chart	
1	White/Blue Stripe & Blue
2	White/Orange Stripe & Orange
3	White/Green Stripe and Green
4	White/Brown Stripe and Brown
Mechanical Characteristics (Overall)	
Installation Temperature Range	0°C To +60°C
Operating Temperature Range	-20°C To +60°C
Max. Recommended Pulling Tension	35 lbs.
Applicable Specifications and Agency Compliance (Overall)	
Applicable Standards & Environmental Programs	
NEC/(UL) Specification	CMP
NEC Articles	800
CEC/C(UL) Specification	CMP
Other Standards	ISO/IEC 11801 ed 2.1 (2008) Class D
EU CE Mark	Yes
EU Directive 2011/65/EU (ROHS II)	Yes
EU Directive 2000/53/EC (ELV)	Yes
EU Directive 2002/95/EC (RoHS)	Yes
EU RoHS Compliance Date (mm/dd/yyyy)	1/1/2004
EU Directive 2002/96/EC (WEEE)	Yes
EU Directive 2003/11/EC (BFR)	Yes
CA Prop 65 (CJ for Wire & Cable)	Yes
MII Order #39 (China RoHS)	Yes
Telecommunication Standards	Category 5e - TIA 568.C.2
Other Specification	NEMA WC-63.1 Category 5e, UL Verified to Category 5e
Flame Test	
UL Flame Test	NFPA 262 Plenum Flame Test (UL910)(FT6)
C(UL) Flame Test	FT6
CSA Flame Tes	FT6

Suitability	
Suitability - Indoor	Yes
Suitability - Outdoor	No
Sunlight Resistance	No
Oil Resistance	No
Plenum/Non-Plenum	
Plenum (Y/N)	Yes

Electrical and Electronic Wire & Cable • Enterprise Cabling & Security Solutions • OEM Supply – Fasteners
Anixter Inc. World Headquarters • 2301 Patriot Boulevard, Glenview, IL 60026-8020 • 1.800.ANIXTER • 224.521.8000 • anixter.com

Anixter is a leading global distributor of enterprise cabling and security solutions, electrical and electronic wire and cable, and OEM supply – fasteners and other small parts.

We reduce risk, complexity and cost from our customers' purchasing decisions, business processes and supply chains.

Anixter does not manufacture these products. Any product warranties are provided by the applicable manufacturers. Data and suggestions made are not to be construed as recommendations to purchase or as authorizations to use any products in violation of any law or regulation. TO THE FULLEST EXTENT PERMITTED BY LAW, ANIXTER DISCLAIMS ALL WARRANTIES, EITHER EXPRESS OR IMPLIED. ANIXTER MAKES NO WARRANTY OR REPRESENTATION, EXPRESS OR IMPLIED, ABOUT THE ACCURACY OR COMPLETENESS OF ANY INFORMATION PROVIDED.