


SOLUTIONS SHEET

Structured Cabling Support Solutions

Chatsworth Products, Inc. (CPI) delivers innovative, high quality and cost effective Structured Cabling Solutions for optimizing, storing and securing network cabling and equipment in both large and small applications. Combine CPI Rack Systems, Cable Management Products, Cable Runway and Tray and Grounding and Bonding Products to support standard wiring closets, or use Wall-Mount Systems to support smaller networks and zone applications.

Make the choice to simplify everyday cabling concerns with CPI's comprehensive Structured Cabling Solutions.



1 13902-703
Velocity Single-Sided
Cable Manager
80.5"H x 6"W x 9.8"D
(2045 mm x 152 mm x 249 mm)

2 55053-703
Standard Rack,
45U x 19"EIA,
7'H x 20.3"W x 15"D
(2.1 m x 516 mm x 380 mm)

3 10250-712
Universal Cable Runway
1.5"H x 12"W x 9'-11.5"L
(38 mm x 300 mm x 3035 mm)

4 40153-020
Busbar
4"H x 20"W x 1/4"D
(100 mm x 510 mm x 6.4 mm)

5 13050-712
ThinLine II Wall-Mount Cabinet
26"H x 26"W x 8.5"D, 4U
(660 mm x 660 mm x 216 mm)

1 Cable Management Products - Velocity® Cable Management is an economical solution for everyday use in telecommunications rooms, equipment rooms and lab spaces and that creates a complete vertical and horizontal pathway for premise cabling and patch cords on CPI Rack Systems.

2 Rack Systems - Unsurpassed strength, stability and durability for supporting patch panels, high-density blocks, cabling and other equipment. With the addition of shelves and special brackets, racks can be quickly adapted for changing needs or to hold larger devices and computer hardware.

3 Cable Runway and Tray - CPI's Cable Runway and OnTrac® Wire Mesh Cable Tray System make up a vital part of the IT infrastructure solution by providing horizontal, vertical and backbone pathways from the data center to workstations.

4 Grounding and Bonding Products - CPI's comprehensive line of UL® Listed Grounding and Bonding Products bond racks, cable runway and tray, and provide protection for electronic equipment.

5 Wall-Mount Systems - Store and secure equipment on the wall inside or outside of the data center or equipment room and connect remote groups of users to the network.

+1-800-834-4969

techsupport@chatsworth.com
www.chatsworth.com

ORDERING INFORMATION

Rack Systems

CPI Rack Systems		
Part Number	Description H x W x D in (mm)	Shipping Weight lb (kg)
55053-703	Standard Rack, 45U x 19"EIA 7'H (2.1 m) x 20.3 x 15 (516 x 380), 1,000 lb (453.6 kg) load, UL Listed, Black	31 (14.1)
48353-703	Universal Rack, 45U x 19"EIA 7'H (2.1 m) x 20.3 x 15 (516 x 380), 1,500 lb (680.4 kg) load, UL Listed, Black	39 (17.7)
15218-703	Adjustable QuadraRack®, 45U x 19"EIA 7'H (2.1 m) x 20.3 (516), Adjustable Depth 36.42 to 42.32 (925 to 1075), 2,000 lb (907.2 kg) load, Black	54 (24.5)

Other sizes and configurations available. Contact CPI at +86-21-6880-0266.

Cable Management Products

Velocity® Single-Sided Vertical Cable Managers		
Part Number	Description H x W x D in (mm)	Shipping Weight lb (kg)
For 7'H (2.1 m), 45U Racks		
13901-703	80.5 x 3.6 x 9.7 (2045 x 91 x 246), Black	18 (8.2)
13902-703	80.5 x 6 x 9.8 (2045 x 152 x 249), Black	20 (9.1)
13904-703	80.5 x 10 x 10.3 (2045 x 254 x 262), Black	32 (14.5)
13905-703	80.5 x 12 x 10.4 (2045 x 305 x 264), Black	34 (15.4)
Velocity® Double-Sided Vertical Cable Managers		
For 7'H (2.1 m), 45U Racks		
13911-703	80.5 x 3.6 x 16.4 (2045 x 91 x 417)	25 (11.3)
13912-703	80.5 x 6 x 16.6 (2045 x 152 x 422)	28 (12.7)
13914-703	80.5 x 10 x 17.5 (2045 x 254 x 445)	40 (18.1)
13915-703	80.5 x 12 x 17.8 (2045 x 305 x 446)	43 (19.5)
Velocity® Horizontal Cable Managers		
13930-701	1U x 19" EIA x 5.9 (150)	2 (0.9)
13930-702	2U x 19" EIA x 5.9 (150)	3 (1.4)
13930-703	3U x 19" EIA x 5.9 (150)	3 (1.4)

Other sizes available. Contact CPI at 800-834-4969.

Velocity® Standard Pack		
Part Number	Description	Shipping Weight lb (kg)
Rack, Cable Management & Hardware Package		
57011-703	(1) Standard Rack, 45U x 19" EIA, UL Listed, Black (1) Velocity® Single-Sided Vertical Cable Manager, 3.6"W (91 mm), Black (1) Rack Installation Kit for concrete floor, 1/2" hardware, Zinc	47 (21.3)
57012-703	(1) Standard Rack, 45U x 19" EIA, UL Listed, Black (1) Velocity® Double-Sided Vertical Cable Manager, 3.6"W (91 mm), Black (1) Rack Installation Kit for concrete floor, 1/2" hardware, Zinc	60 (27.2)
57013-703	(1) Standard Rack, 45U x 19" EIA, UL Listed, Black (1) Velocity® Single-Sided Vertical Cable Manager, 6"W (152 mm), Black (1) Rack Installation Kit for concrete floor, 1/2" hardware, Zinc	50 (22.7)
57014-703	(1) Standard Rack, 45U x 19" EIA, UL Listed, Black (1) Velocity® Double-Sided Vertical Cable Manager, 6"W (152 mm), Black (1) Rack Installation Kit for concrete floor, 1/2" hardware, Zinc	68 (30.8)

Not exactly what you need? Additional products, sizes and configurations are available from CPI. Visit www.chatsworth.com or call +1-800-834-4969.

Cable Runway and Tray

Cable Runway		
Part Number	Description H x W x L in (mm)	Shipping Weight lb (kg)
10250-712	Universal Cable Runway 1.5 x 12 (38 x 300) x 9'-11.5"L (3 m)	25 (11.3)
10250-718	Universal Cable Runway 1.5 x 18 (38 x 460) x 9'-11.5"L (3 m)	29 (13.2)
11301-701	Butt-Splice Kit (end-to-end splice)	1 (0.5)
11302-701	Junction-Splice Kit (L or T intersection)	1 (0.5)
10506-706	Cable Runway Elevation Kit, 4", 5" or 6"H (100 mm, 130 mm or 150 mm)	3 (1.4)
12730-712	Rack-To-Runway Mounting Plate, For 12"W (300 mm) Runway, Black	5 (2.3)
12730-718	Rack-To-Runway Mounting Plate, For 18"W (460 mm) Runway, Black	7 (3.2)
11421-712	Wall Angle Support Kit, For 12"W (300 mm) Runway, Black	7 (3.2)
11421-718	Wall Angle Support Kit, For 18"W (460 mm) Runway, Black	7 (3.2)
11310-093	Threaded Ceiling Kit, with M10 x 2m L Rod	3 (1.4)
OnTrac® Wire Mesh Cable Tray		
34811-512	Tray, 2 x 12 (50 x 300) x 10'L (3 m), Zinc Plated	17 (7.7)
34821-512	Tray, 4 x 12 (100 x 300) x 10'L (3 m), Zinc Plated	21 (8.5)
34738-501	Standard Splice Kit, Pack of 50	11 (5.0)
34746-501	Clamp Washer, Pack of 25	2 (0.9)
34730-512	Trapeze Support Bracket, For 12"W (300 mm) Tray	2 (0.9)

Grounding and Bonding

Part Number	Description H x W x D in (mm)	Shipping Weight lb (kg)
40153-020	Busbar, 4 x 20 x 1/4 (100 x 510 x 6.4)	8 (3.6)
10610-019	Horizontal Rack Busbar, 19" EIA	2 (0.9)
40161-072	Vertical Rack Busbar Kit	7 (3.2)
40164-025	Cable Runway Ground Strap Kit, #6 AWG, Pack of 25	12 (5.0)

Wall-Mount Systems

Part Number	Description H x W x D in (mm)	Shipping Weight lb (kg)
13602-708	EasySwing Wall-Mount Rack, 11U x 19"EIA x 6.5 (35), 24.5 x 20.3 x 8.0 (622 x 516 x 200), 100 lb (45.4 kg) load, Black	22 (10.0)
13050-712	4U x 19"EIA, ThinLine II Wall-Mount Cabinet, 26 x 26 x 8.5 (660 x 660 x 216)	54 (24.5)
13051-001	Intelligent Fan Kit, 115 VAC, 60 Hz	2 (0.9)

Accessories

Part Number	Description	Shipping Weight lb (kg)
40074-700	Single-Sided Shelf, 3U x 19"EIA x 15"D (380 mm), 50 lb (22.7 kg) load, Black	6 (2.7)
40108-719	Double-Sided Shelf, 4U x 19"EIA x 21.5"D (546 mm), 100 lb (45.4 kg) load, Black	8 (3.6)

