

FT8316/FR8316 Fiber Transmitter and Receiver

SIXTEEN-CHANNEL DIGITALLY ENCODED VIDEO

Product Features

- 8-Bit Digitally Encoded Video for High-Quality Multichannel Video Transmission over a Single Fiber
- Multimode Fiber Support for Distances up to 1 km
- Single-Mode Fiber Support for Distances up to 26 km
- Exceeds All Requirements for the RS-250C Medium-Haul Transmission Specification
- Compatible with NTSC, PAL, and SECAM Video Standards
- Designed to Meet NEMA TS 2 and Caltrans Traffic Signal Control Equipment Environmental Standards
- No Performance Adjustments Required
- 12 VDC or 24 VAC Power Supply
- Stand-Alone and Rack-Mountable Modular Design
- LED Indicators for Monitoring of Signal Status, Laser Status, and Operating Power



The **FT8316/FR8316** fiber transmitter and receiver provide the ability to transmit up to 16 composite video channels over one optical fiber. The **FT8316** transmitter and the **FR8316** receiver are available in multimode and single-mode versions.

Modular in design, the **FT8316** and **FR8316** units can be rack mounted or can be used as stand-alone modules. Rack mounting is accomplished using the RK5000 Series rack mount chassis. Stand-alone modules can be placed on a desktop or can be mounted to a wall. The WM5004-3U wall mount kit is required to mount an **FT8316** or **FR8316** unit to a wall.



C2603 / NEW 6-06



International Standards
Organization Registered Firm,
ISO 9001 Quality System



TECHNICAL SPECIFICATIONS

MODELS

Model No.		Fiber Optic Connector Type	Wavelength	Optical Power Budget	Maximum Transmission Distance
Transmitter	Compatible Receiver				
Multimode (62.5/125 μm)					
FT8316MSTR	FR8316MSTR	ST	1275 nm 1300 nm	18 dB*†	1 km (0.6 mi)‡
Single-Mode (9/125 μm)					
FT8316SSTR	FR8316SSTR	ST	1275 nm 1300 nm	18 dB	26 km (16.1 mi)§
FT8316SFCR	FR8316SFCR	FC	1275 nm 1300 nm	18 dB	26 km (16.1 mi)§

*Optical power budget is 15 dB when operating temperature range is -40° to 0°C.

†When using 50/125 µm multimode fiber, subtract 3 dB from the optical power budget.

‡Maximum transmission distance is limited by fiber bandwidth.

§Maximum transmission distance is based on attenuation of 0.5 dB/km plus a 5 dB buffer for connector and splice losses.

Notes:

- For conformal coated models, replace the first letter *F* in the model number with the letter *C*. The conformal coated version of FT8316MSTR, for example, is CT8316MSTR.
- For models with higher optical power budgets, contact the factory.

Supplied Accessories

Regulated switching power supply with either of the following:

- Four plug adapters (North American, Australian, United Kingdom, and European); 100-240 VAC, 50-60 Hz input, 12 VDC (25 W) output

or

- Three power cords (North American, United Kingdom, and European); 100-240 VAC, 47-63 Hz input, 12 VDC (24 W) output

Note: In extreme temperature conditions, it is recommended that an industrial-rated outdoor power supply such as the Pelco® WCS1-4 power supply be used.

VIDEO

Number of Channels	16
Modulation Type	Pulse code modulation, 8-bit resolution
Video Input (FT8316)/ Video Output (FR8316)	1.0 Vp-p, 75 ohms; NTSC, PAL, and SECAM
Bandwidth	6.5 MHz
Gain	Unity
Crosstalk	-50 dB typical at 3.58 MHz
Differential Gain	<1%
Differential Phase	<1.2°
Tilt	<1%
Signal-to-Noise Ratio	>60 dB (CCIR weighted)

GENERAL

Operating Temperature	-40° to 167°F (-40° to 75°C)
Input Power Requirements	12 VDC or 24 VAC, 900 mA
LED Indicators	Power Video Present (per channel) Optic Fault (one LED for channels 1-8, one LED for channels 9-16)
Dimensions	8.75" D x 4.68" W x 4.81" H (22.23 x 11.89 x 12.22 cm)
Unit Weight	4 lb (1.81 kg)
Shipping Weight	7 lb (3.18 kg)

MECHANICAL

Connectors

Video	BNC (per channel)
Rack Power/Alarm	4-pin connector
Stand-Alone Power	2-pin connector, screw terminal
Fiber Optic	ST for multimode fiber ST or FC for single-mode fiber

CERTIFICATIONS

- CE, Class A
 - UL Listed
 - UL Listed to Canadian safety standards
 - FCC, Class A
 - C-Tick
 - Complies with FDA requirements for Class 1 laser products
 - Designed to meet NEMA TS 2 and Caltrans traffic signal control equipment standards for ambient operating temperature, mechanical shock and vibration, humidity with condensation, high-line/low-line voltage conditions, and transient voltage protection (certification pending)
- Note:** Conformal coating is required for operation in environments with relative humidity above 95% (condensing).

OPTIONAL ACCESSORIES

WM5004-3U	Wall mount kit for quadruple-width module
RK5000-3U	19-inch rack mount chassis for 14 slots, no power (3 RUs)
RK5000PS-3U	19-inch rack mount chassis for 12 slots with power (3 RUs)
EPS5000-120	External rack power supply, 1 RU, dual 120 W power outputs
RK5001B-3U	Blank filler panel, single width
RK5002B-3U	Blank filler panel, double width
RK5004-1UEXP	Adapter kit that allows a 3 RU quadruple-width fiber module to be used in RK5000PS-5U rack mount chassis



Pelco, Inc. Worldwide Headquarters:

3500 Pelco Way, Clovis, California 93612-5699 USA

USA & Canada Tel: (800) 289-9100 • FAX: (800) 289-9150

International Tel: +1 (559) 292-1981 • FAX: +1 (559) 348-1120

www.pelco.com

Pelco and the Pelco logo are registered trademarks of Pelco, Inc.
Product specifications and availability subject to change without notice.
©Copyright 2006, Pelco, Inc. All rights reserved.