

DS484Q and DS486Q Quad-Beam Photoelectric Detectors

www.boschsecurity.com



BOSCH
Invented for life



- ▶ Quad beams
- ▶ Easy alignment (sounder, LEDs, and voltage readings)
- ▶ Two coverage ranges
- ▶ Four mounting options with optional mounting poles
- ▶ Environmental discrimination circuit

The DS484Q and DS486Q Detectors have separate transmitters and receivers. The transmitter sends an invisible infrared beam to the receiver. If the beam is broken, the receiver signals an alarm. Multiple channel operation provides increased system flexibility.

Functions

Environmental Discrimination Circuitry

Monitors gradual loss of signal due to dust, fog, rain, snow, and so on. Normally-closed output opens when signal loss reaches 90%. Can be field configured to bypass alarm relay when activated.

Test Features

The transmitters have three features for use in alignment and testing.

- Voltage output (requires a voltmeter)
- Sounder for alignment
- LEDs (alignment)

Multiple Channel Operation

Configure the detectors for up to eight different channels. This allows multiple units to be used near one another without the possibility of receiver cross-talk. This is particularly useful when stacking multiple beam sets.

And-Or Mode Selection

You can configure the detectors to cause an alarm when all four beams are blocked, or when either the upper two beams or lower two beams are blocked. This configuration detects smaller objects and eliminates the possibility of someone crawling through the beam.

Certifications and approvals

Region	Certification	
Europe	CE	89/336/EEC, EN55022: 1998, EN50130-4: 1995 +A1: 1998 +A2: 2003, EN61000-3-2: 2000, EN61000-3-3: 1995, EN61000-4-2: 1995 +A1: 1998 +A2: 2001, EN61000-4-3: 1996 +A1: 1998 +A2: 2001, EN61000-4-4: 1995 +A1: 2001, EN61000-4-5: 1995 +A1: 2001, EN61000-4-11: 1994, EN50141: 1993
USA	UL	ANSR: Intrusion Detection Units (UL639)

Installation/configuration notes**Mounting Considerations**

Mount these detectors on solid vibration free surfaces or poles.

Technical specifications**Photobeam**

Selectable Beams:	Two groups by four channels
Maximum Outdoor Coverage DS484Q:	120 m (400 ft)
Maximum Outdoor Coverage DS486Q:	200 m (660 ft)
Response Time:	Selectable response time of 35 ms to 700 ms
Beam Interrupt Time:	Adjustable from 50 ms to 500 ms

Enclosure Design

Material:	Polycarbonate
Dimensions:	398 mm x 103 mm x 99 mm (15.67 in. x 4.06 in. x 3.90 in.)
Receiver Weight:	1.2 kg (2.64 lb)
Transmitter Weight:	1.2 kg (2.64 lb)

Environmental Considerations

Operating Temperature:	-25° C to + 55° C (-13°F to + 130°F)
IP Rating:	IP 54 (protection against dust; protection against splashing water)

Mounting Considerations

Location:	Surface or pole mount
Pattern Pointability:	±90° horizontal, ±10° vertical

Power Requirements

Voltage:	10.5 VDC to 28 VDC non-polarized
Receiver Current Draw:	80 mA standby, 50 mA alarm
DS484Q Transmitter Current Draw:	35 mA
DS486Q Transmitter Current Draw:	55 mA
Backup Power Requirements:	4 hours (120 mAh) minimum required for UL Certificated Installations
Tamper Output:	Normally-closed contacts rated at 0.1 A at 30 VDC
Alarm Output:	Form C 0.2 A at 30 VDC, output period: 3 sec
EDC Output:	Normally-closed 0.2 A at 30 VDC, output period: 3 sec
Tamper Output:	Normally-closed 0.1 A at 30 VDC, output period: while cover is removed
Environmental Discrimination Circuit Output:	Normally-closed contacts rated at 0.2 A at 30 VDC

Ordering information**DS484Q Photoelectric Detector**

Provides an outdoor range of 120 m (400 ft).
Order number **DS484Q**

DS486Q Photoelectric Detector

Provides an outdoor range of 200 m (660 ft).
Order number **DS486Q**

Accessories**MP1 Metal Pole, 1 m (3 ft)**

Straight metal poles measuring 1 m (3 ft) for pole mounting photoelectric detectors. Shipped in packages of two.
Order number **MP1**

MP2 Metal Pole, 1.2 m (4 ft)

Straight metal poles measuring 1.2 m (4 ft) for pole mounting photoelectric detectors. Shipped in packages of two.
Order number **MP2**

MP3 L-Curved Metal Pole

Curved metal poles for mounting to vertical surfaces for pole mounting photoelectric detectors. Shipped in packages of two.
Order number **MP3**

PC1A Weather Enclosure

Protects detectors when mounted outside. The enclosure's dimensions are 39.4 cm x 10.3 cm x 6 cm (15.5 in. x 4 in. x 2.4 in.). Shipped in packages of two.
Order number **PC1A**

PC3A Back-to-back Box

Allows back-to-back mounting of detectors on a pole.

Shipped individually.

Order number **PC3A**

PEH-2 Heater

Reduces the effects of frost, intense fog, cold, and damp conditions on photoelectric beam detectors.

Shipped in packages of two (one for transmitter and one for receiver).

Order number **PEH2**

Represented by:

Americas:

Bosch Security Systems, Inc.
130 Perinton Parkway
Fairport, New York, 14450, USA
Phone: +1 800 289 0096
Fax: +1 585 223 9180
security.sales@us.bosch.com
www.boschsecurity.us

Europe, Middle East, Africa:

Bosch Security Systems B.V.
P.O. Box 80002
5617 BA Eindhoven, The Netherlands
Phone: + 31 40 2577 284
Fax: +31 40 2577 330
emea.securitysystems@bosch.com
www.boschsecurity.com

Asia-Pacific:

Robert Bosch (SEA) Pte Ltd, Security Systems
11 Bishan Street 21
Singapore 573943
Phone: +65 6571 2808
Fax: +65 6571 2699
apr.securitysystems@bosch.com
www.boschsecurity.asia

China:

Bosch (Shanghai) Security Systems Ltd.
201 Building, No. 333 Fuquan Road
North IBP
Changning District, Shanghai
200335 China
Phone +86 21 22181111
Fax: +86 21 22182398
www.boschsecurity.com.cn

America Latina:

Robert Bosch Ltda Security Systems Division
Via Anhanguera, Km 98
CEP 13065-900
Campinas, Sao Paulo, Brazil
Phone: +55 19 2103 2860
Fax: +55 19 2103 2862
latam.boschsecurity@bosch.com
www.boschsecurity.com