




THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



SECTION VIEW OF CRIMPED DISCONNECT

NOTES:

1. UL LISTED AND CSA CERTIFIED FOR:
A. 600V MAX VOLTAGE RATING
B. 221°F (105°C) MAX TEMP RATING
C. STRANDED COPPER WIRE ONLY
D. 6-12 LBS INITIAL INSERTION/WITHDRAWAL FORCE
2. PACKAGE QTY: -M=1000 PIECES, -C=100 PIECES
3. MATERIAL:
A. STAMPING-CDA 260 BRASS, TIN PLATED
B. HOUSING-PREMIUM GRADE NYLON FOR SUPERIOR STRAIN RELIEF INSULATION CRIMPING
4. DIMENSIONS IN BRACKETS ARE IN mm OR mm²
5. NYLON HOUSING IS OPAQUE
6. WIRE STRIP LENGTH: $7/32'' \pm .1/32''$ ($5.6 \pm .0.8$)



LISTED
20H3
E78522



CERTIFIED
LR31212

PART NUMBER	PKG. SUFFIX	TAB SIZE	WIRE RANGE AWG (MM)	COLOR (note 5)	MAX. INSUL. DIA.	MIN. INSUL. DIA.	DIMENSIONS in.			TOOL CHART
							A $\pm .02$	B $\pm .01$	C $\pm .02$	
DPF18-110F1B	-C	.110 X .032 (2,8 X 0,8)	22-18 (0,5-1,0)	RED	.132 (3,35)	.080 (2,03)	.71 (18,0)	.19 (4,83)	.16 (4,06)	CT-520 CT-1525 (USE POCKET "A")
DPF18-111F1B	-M	.110 X .020 (2,8 X 0,5)	22-18 (0,5-1,0)	RED	.132 (3,35)	.080 (2,03)	.71 (18,0)	.19 (4,83)	.16 (4,06)	

07	2/07	DAW	DAW	ADDED POCKET "A" NOTE TO CT-1525	TR00220	LCA	TRO	A41464_07			
06	7/03	KLFU	SKB	UPDATED GEOMETRY WIRE RANGE WAS 0,5-1,5	12453	LCA	TRO	PANDUIT CORP. TINLEY PARK, ILLINOIS			
05	1/01	RM	SKB	FILESPEC WAS N41464AA_PCD_04	8933	JAC	CCH				
04		JKD		ADDED CT-1525 TOOL	07632			DISCOGRIP™ LOOSE PIECE FULLY INSULATED FEMALE DISCONNECTS .110 X .032, .110 X .020			
03	10/96	TM	RLS	UPDATED NOTES AND DIMENSIONS	05139	LA	DBH				
REV	DATE	BY	CHK	DESCRIPTION	ECN#	CUST	PM	DRAWN BY RPH	CHK'D	SCALE NONE	DRAWING NO./CAD FILENAME A41464