


HS1500 Enclosure

HIGH SECURITY, INDOOR, CORNER MOUNT

Product Features

- Vandal Resistant
- Indoor, Corner Mount Applications
- All-Steel Construction
- No Exposed Mounting Hardware
- Tamper Switch Standard Feature




The **HS1500** high security enclosure is designed for applications such as elevators, parking garages, classrooms, detention cells, etc., requiring maximum protection from vandalism. Designed to fit flush to the ceiling in a corner, the enclosure includes an impact-resistant clear Lexan® window as a standard feature.

The **HS1500** is constructed of heavy gauge steel and will accept most CCD cameras with fixed focal length and varifocal lenses.

There is no exposed mounting hardware securing the enclosure to its mounting surface. Opening the enclosure can be accomplished only by removing the tamper-resistant screw from the bottom with the specially designed tool provided, eliminating the possibility of the enclosure being opened by unauthorized personnel. A tamper-switch is mounted on the secured access cover.

 VALUES IN PARENTHESES ARE INCHES; ALL OTHERS ARE CENTIMETER:



TECHNICAL SPECIFICATIONS

MODEL

HS1500	High security corner mount enclosure of medium size; designed to fit flush with the ceiling
--------	---

MECHANICAL

Camera Mounting	Adjustable tilt table
Maximum Camera and Lens Size	Accepts camera and lens combinations* (including BNC connector) up to: 10.16 x 10.16 x 20.32 cm (4.0" H x 4.0" W x 8.0" L)
Enclosure Mounting	Four 0.99 cm (0.390-inch) diameter holes on protected rear surface
Cable Entry	Access through back and top
Security	Tamper-resistant screw (hollow Allen wrench supplied)
Tamper Switch	Plunger type door switch with "pull-to-cheat" feature; DM electrical rating 10 A, 125 VAC; N.O./N.C. switch contact

*Assumes lens is fully extended.

ELECTRICAL

Tamper Switch	0.63 cm (0.25-inch) quick connect N.O./N.C. 10 A maximum switching current 125 VAC maximum switching voltage
---------------	--

GENERAL

Window	12.70 mm (0.50-inch) thick Lexan®
Construction	3.40 mm (0.134-inch) formed, 10-gauge steel
Finish	Gray polyester powder coat
Environment	Indoor; 0° to 49°C (32° to 120°F)
Unit Weight	7.88 kg (17.37 lb)
Shipping Weight	9.06 kg (20 lb)

CERTIFICATIONS/RATINGS

- UL Listed
- Meets NEMA Type 1 standards

OPTIONAL ACCESSORIES

HB1524	Heater-blower kit; 24 VAC, 85 W; heater activates on at 4°C (40°F) and off at 15°C (60°F); blower provides continuous internal air circulation
--------	--