


## Fan Module for Wall Mount Enclosures



**Operating Voltage** AC 220 - 240 Volts 50/60 Hz

**Standards** Conforms to IEC 297-1 **Air Flow** 95 -115 CFM

**Noise** 44 - 49 dB (A) **Material** 0,8 mm Steel

**Fan Speed** 2700 - 3100 rpm **Finish** Electrostatic Powder Paint

**Packaging** One piece in a box

H (mm)	D (mm)	W (mm)	Number of Fans	Weight kg	Part No
39	135	326	1	1,27	CWA-X-2001
39	135	326	2	1,80	CWA-X-2002



[www.facebook.com/canovategroup](http://www.facebook.com/canovategroup)



[www.linkedin.com/company/canovate-group](http://www.linkedin.com/company/canovate-group)



[canovatesales](https://twitter.com/canovatesales)