

Technical drawing of a wire joint assembly, showing two views: a side view and a cross-sectional view.

Side View Dimensions and Labels:

- P MIN.:** Minimum thickness of the top flange.
- G:** Distance from the center of the hole to the edge of the top flange.
- C REF.:** Reference dimension for the top flange.
- W:** Width of the top flange.
- A:** Total length of the component.
- D DIA.:** Diameter of the central hole.
- Labels:** PANDUIT, LA 300, 300 AL-C, BLUE DIE.

Cross-sectional View Dimensions and Labels:

- T:** Thickness of the top flange.
- B (INTERNAL):** Internal length of the component.
- E DIA.:** Diameter of the wire entry.
- Labels:** PLASTIC PLUG, OXIDE INHIBITOR JOINT COMPOUND, 26° BEVELED WIRE ENTRY.

- 1. MATERIAL - SEAMLESS ALUMINUM TUBING.**
- 2. TIN PLATED.**
- 3. BARREL COLOR CODED WITH DIE SET INDEX NUMBER.**
- 4. UL LISTED.**
- 5. CSA CERTIFIED.**
- 6. FOR STRANDED ALUMINUM AND COPPER WIRE.**
- 7. ALL DIMENSIONS ARE IN INCHES.**

UL
LISTED
587H
E52164


CERTIFIED
LR31212

C41129_04

[illegible]