



51110-PTC



UPC Code: 07847706633

Country of Origin: Mexico - *Eligible for
ARRA funded projects > \$7,443,000



Whole House Surge Protection from Leviton

Brand Features

Panel-Mounted Surge Protective Devices (SPD)- Provides homes with protection from high-energy transient voltage appliances. DHC components incorporate micro-circuitry and Leviton highly recommends protecting the DHC network from power line surges. Leviton panel-mounted surge protective devices feature unique hybrid suppression circuitry for outstanding surge protection. The following devices are compatible with all DHC components. Single Phase Multi-Media Panel: Provides surge protection for AC power line, 2 pairs of phone/fax/modem connections and dual CATV/satellite feeds using F connectors

Item Description

120/240 Volt Panel Protector, 4-Mode Protection, 48kA Max Surge Current Rating, Residential Grade, 2 Pair Tele/Fax/Modem Dual CATV/Sat Type F, NEMA 1 Enclosure

Technical Information

Electrical Specifications

Voltage Configuration: 120/240V Single Phase

Surge Technology: MOV

Frequency: 50/60Hz

EMI/RFI Noise Rejection: (-6 to -28dB @ 100KHz to 100MHz)

Recommended Circuit Breaker Rating: 30A, 120/240V

Environmental Specifications

Enclosure Rating: NEMA 1

Flammability: Rated V-2 per UL94

Operating Temperature: -10C to 60C

Storage Temperature: -20°C to 85°C

Relative Humidity: 5% to 95% non-condensing

Material Specifications

Outer Enclosure: Powder Coated Steel

Mechanical Specifications

Connection Type: Hardwired Parallel Connection

Diagnostics: Protection Status LEDs

Performance Data

MCOV: L-N:150V, L-G:150V, N-G:150V, L-L:300V

VPR: L-N:600V, L-G:600V, N-G:600V, L-L:1000V

Nominal Discharge Current Rating: 3kA

Maximum Surge Current, Per Mode (Per Phase): 48kA (96kA)

Short Circuit Current Rating: 10KA

Product Features

Diagnostics: LED

Feature: 2 Pair Tele/Fax/Modem Dual CATV/Sat Type F

Modules: Fixed

MCOV: 150V AC

Max Surge Current kA L-N: 48kA

Standards and Certifications

UL1449 3rd Edition: cULus Listed Type 2

ANSI/IEEE Category A, B & C: C-62.41 & 62.45

Warranty

Product Warranty: 10-Year Limited

SPECIFICATION SUBMITTAL

JOB NAME:	CATALOG NUMBERS:	
<input type="text"/>	<input type="text"/>	<input type="text"/>
JOB NUMBER:	<input type="text"/>	<input type="text"/>

Leviton Manufacturing Co., Inc.

201 North Service Road, Melville, NY 11747

Telephone: 1-800-323-8920 • FAX: 1-800-832-9538 • Tech Line (8:30AM-7:30PM E.S.T. Monday-Friday): 1-800-824-3005

Leviton Manufacturing of Canada, Ltd.

165 Hymus Boulevard, Pointe Claire, Quebec H9R 1E9 • Telephone: 1-800-469-7890 •

FAX: 1-800-824-3005 • www.leviton.com/canada

Leviton S. de R.L. de C.V.

Lago Tana 43, Mexico DF, Mexico CP 11290 • Tel.: (+52)55-5082-1040 • FAX: (+52)5386-1797 • www.leviton.com.mx

Visit our Website at: www.leviton.com

© 2012-2015 Leviton Manufacturing Co., Inc. All rights reserved. Subject to change without notice.

**Leviton has a global presence.**

If you would like to know where your local Leviton office is located please go to: www.leviton.com/international/contacts/

**Buy American Compliant Logo -- The American Recovery And Reinvestment Act of 2009 ("ARRA") provides federal grants and loans for projects throughout the country. Section 1605 of the Act, named the "Buy American" provision, requires that certain materials and manufactured products used in projects funded by the Act be manufactured in the United States. The appearance of the Recovery Act Logo in relation to a Leviton product is only intended to reflect that such product may be used in an ARRA funded project. It does not mean that such product or Leviton is sponsored or endorsed by, or that Leviton receives funds from, the federal government or the Recovery Accountability and Transparency Board. Nothing in Leviton's use of the logo is intended to suggest anything regarding the requirements for funding under ARRA.*