
TX6A^m 10Gig^m Shielded Copper Cable – F/UTP

specifications

Category 6A cable shall be constructed of 23 AWG copper conductors with PE CM, CMR or LSZH insulation. The copper conductors shall be twisted in pairs and separated by an integrated pair separator. All four pairs shall be surrounded by an overall metallic foil shield within a low smoke zero halogen jacket. The TX6A[™] 10Gig[™] Shielded Copper Cable must be installed as part of a complete TX6A[™] 10Gig[™] Shielded Copper Cabling System to achieve 10GBASE-T certified performance.

technical information



key features and benefits

Integrated pair divider:	Separates pairs for exceptional cable performance	
Overall foil shield:	Provides superior structural integrity and reduces low frequency external interference to ensure exceptional cable performance at all swept frequencies up to 500 MHz	
Internal drain wire:	Facilitates means of grounding the cable and provides for efficient performance and protection of network investment	
Descending length cable markings:	Easy identification of remaining cable reduces installation time and cable scrap	
Bulk packaging:	Supplied 305m (1000 ft.) to a reel	

applications

TX6A[™] 10Gig[™] Shielded Copper Cable is a component of the Panduit® TX6A™ 10Gig™ Shielded Copper Cabling System. This end-to-end system provides a cost-effective medium for ensuring that network bandwidth needs are easily met today and tomorrow. The shielded cabling system provides high performance, excellent EMI suppression, and aids in secure data transmission. The Panduit solution helps

www.panduit.com

ensure organizations efficiently and reliably meet their data transmission needs. Usage of the TX6A™ 10Gig[™] Shielded Copper Cabling System include high bandwidth applications within data centers and connections to high-end workstations such as:

- 10GBASE-T Ethernet
- Data Center applications
- Virtual business management applications




TX6A [™] 10Gig [™] Shielded Copper	Cabling System			
TX6A [™] 10Gig [™] Shielded Coppel	r Cable – F/UTP			
LSZH: CM: CMR: CMP:	PFL6X04*-CEG PFC6X04*-CEG PFR6X04*-CG PFP6X04*-UG			
TX6A [™] 10Gig [™] Shielded Jack Me	odule			
Jack Module:	CJS6X88TGY			
TX6A [™] 10Gig [™] Shielded Patch Cords				
Meters: Feet:	STP6X**MIG STP6X***IG			
Mini-Com [®] Angle Shielded Modula	ed All Metal r Patch Panels			
24-port, 1 RU: 48-port, 2 RU: 72-port, 2 RU:	CPA24BLY CPA48BLY CPA72BLY			
Mini-Com [®] Flat A Modular Patch Pa				
24-port, 1 RU: 48-port, 2 RU: 72-port, 2 RU:	CP24BLY CP48BLY CP72BLY			
Cable Prep Tools				
Wire snipping to Wire stripping to				
*To designate color, add (White). For additional o customer service.	d suffix BU (Blue) or WH cable colors, contact			
meter) and 1.5, 2.5, 15, length designation in th length. For standard ca	**For lengths 1 to 10 meters (increments of one meter) and 1.5, 2.5, 15, 20 meters, change the length designation in the part number to desired length. For standard cable colors other than IG (International Grav) substitute IG suffix with			

IG (International Gray) substitute IG suffix with BL (Black), BU (Blue), GR (Green), RD (Red), YL (Yellow), OR (Orange) or VL (Violet) to the end of the part number, For example, the part number for a blue, 15-meter patch cord is STP6X15MBU.

***For lengths 3 to 20 feet (increments of one foot) and 25, 30, 35, 40 feet, change the length designation in the part number to desired length. For standard cable colors other than IG (International Gray) substitute IG suffix with BL (Black), BU (Blue), GR (Green), RD (Red), YL (Yellow), OR (Orange) or VL (Violet) to the end of the part number. For example, the part number for a blue, 15-foot patch cord is STP6X15BU.

TX6A^m 10Gig^m Shielded Copper Cable – F/UTP

	LSZH	СМ	CMR	СМР		
Mechanical Test						
Ultimate Breaking Strength	>400 N (90 lbf)					
Minimum Bend Radius	8 x cable diameter during installation 4 x cable diameter during operation					
		Electrical Test				
Mutual Capacitance	<5.6 nF per 100m (328 ft.) at 1 Khz					
Characteristic Impedance	100 Ohm +/-15% up to 100 MHz					
Nominal Velocity of Propagation (NVP)		70% nominal				
DC Resistance	<9.38 ohm per 100m (328 ft.)	<9.50 ohm per 100m (328 ft.)	<7.32 ohm per 100m (328 ft.)	8.9 ohm per 100m (328 ft.)		
DC Resistance Unbalance	<5%	<2%	<5%	<4%		
Capacitance Unbalance	<330 pF per 100m (328 ft.)	<160 pF per 100m (328 ft.)	<330 pF per 100m (328 ft.) at 1 kHz (pair/ground)	<330 pF per 100m (328 ft.) at 1 kHz (pair/ground)		



WORLDWIDE SUBSIDIARIES AND SALES OFFICES

PANDUIT CANADA Markham, Ontario cs-cdn@panduit.com Phone: 800.777.3300 PANDUIT EUROPE LTD. London, UK cs-emea@panduit.com Phone: 44.20.8601.7200

PANDUIT SINGAPORE PTE. LTD. Republic of Singapore cs-ap@panduit.com Phone: 65.6305.7575 PANDUIT JAPAN PAN Tokyo, Japan Gua cs-japan@panduit.com Phone: 81.3.6863.6000 Pho

PANDUIT LATIN AMERICA Guadalajara, Mexico cs-la@panduit.com Phone: 52.33.3777.6000 PANDUIT AUSTRALIA PTY. LTD. Victoria, Australia cs-aus@panduit.com Phone: 61.3.9794.9020

For a copy of Panduit product warranties, log on to www.panduit.com/warranty

For more information

Visit us at www.panduit.com

PANDUIT®

Contact Customer Service by email: cs@panduit.com or by phone: 800.777.3300 ©2012 Panduit Corp. ALL RIGHTS RESERVED. COSP297--WW-ENG 12/2012