

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.







TABLE - 1		
ASSEMBLY PART NUMBER	ITEM DESCRIPTION	WEIGHT
FSCBT2BU-X	OPTICAM 1.6/2.0mm CABLE RETENTION BOOT ASSEMBLY WITH BLUE BOOT	3.53g/10 Pcs [ .125oz/10 Pcs ]
FMCBT2AQ-X	OPTICAM 1.6/2.0mm CABLE RETENTION BOOT ASSEMBLY WITH AQUA BOOT	
FMCBT2BL-X	OPTICAM 1.6/2.0mm CABLE RETENTION BOOT ASSEMBLY WITH BLACK BOOT	



#### NOTES:

1. SEE CURRENT CATALOG FOR PART NUMBER SUFFIXES TO INDICATE COLOR AND/OR PACKAGE QUANTITIES.
2. SEE CATALOG FOR ADDITIONAL INFORMATION PERTAINING TO THESE PRODUCTS.
3. 10 ASSEMBLIES PER PACKAGE.
4. MATERIALS:  
A. RETENTION NUT: PLASTIC  
B. BOOT: RUBBER
5. PRIMARY DIMENSIONS ARE METRIC, DIMENSIONS IN BRACKETS ARE CUSTOMARY.

										OPTICAM 1.6/2.0mm CABLE RETENTION BOOT ASSEMBLY CUSTOMER DRAWING	
										 <b>PANDUIT</b> <sup>TM</sup> CORP. TINLEY PARK, ILL 60477	<small>DRAWING FILENAME</small> MO1799AY_DC_2mmX_00B.prt  <small>SCALE</small> NONE
										<small>ALL DIMENSIONS ARE GIVEN IN INCHES UNLESS OTHERWISE SPECIFIED.</small> <small>DIMENSIONAL TOLERANCES ARE:</small> (.X) (.XXX) ±.010 (.0.3) (.XX) ±.03 (.0.8) ANGLES	<small>PART NO.</small> SEE TABLE 1  <small>DRAWING NO.</small> 01799-45  <small>SIZE</small> A
										<small>THIRD ANGLE PROJECTION</small> 	<small>REVIEW DRAWING NUMBERS</small>
										<small>DRAWN BY</small> MC  <small>DATE</small> 07-31-06  <small>CHK'D</small> JAW	
1	08-08-06	MC		RELEASED TO PRODUCTION	01799-45						
REV	DATE	BY	CHK	DESCRIPTION	ECN	-	R	CUST	SUP	OTH	