

Anixter Level 2 for Industrial Network Environments

Power Supplies: 24V 10 A Single Phase



Anixter Item #	Product Description
L2-24V-10A-1P	DIN Rail Mount Power Supply, Single Phase, 24 VDC / 10A

Input Circuit		
Rated input voltage U	115 / 230 V AC auto select	
Input voltage range	90-132 V AC, 180-264 V AC / 210-375 V DC	
Frequency range AC	47-63 Hz	
Typical input current	at 115 V AC	4.0 A
	at 230 V AC	1.55 A

Typical power consumption		270 W
Inrush current limiting	at 115 V AC	30 A (max. 5 ms)
	at 230 V AC	60 A (max. 5 ms)
Internal input fuse		6.3 A slow-acting / 250 VAC
Power factor correction (PFC)		yes, passive, 0.7
Indication of Operational States:		
Output voltage	Green LED	OUTPUT OK: V: output voltage OK
	Red LED	OUTPUT LOW: V: output voltage too low
Output Circuit		
Rated output voltage		24 V DC
Tolerance of the output voltage		0...+1 %
Adjustment range of the output voltage		22.5-28.5 V DC
Rated output power		240 W
Rated output current I		10 A
Signaling contact for output voltage OK		solid-state (max. 60 VDC, 0.3 A)
Minimum fuse rating to achieve short-circuit protection		M 60 V DC, 0.3 A fast-acting
Output circuit - No-load, overload and short-circuit behavior:		
Power dissipation		typ. 35 W
Efficiency		typ. 89%
Duty time		100%
Dimensions (W x H x D)		83 x 123.6 x
		123.6 mm
		[3.27 x 4.87 x 4.87 in]

Weight	1.334 kg (3.01 lb)	
Material of housing	Metal	
Mounting	DIN rail (IEC/EN 60715), snap-on mounting without any tool	
Mounting position	horizontal	
Degree of protection housing / terminals	IP20 / IP20	
Electrical connection - input circuit / output circuit:		
Wire size fine-strand with wire end ferrule	fine-strand with wire end ferrule	0.2-4 mm ² (24-11 AWG)
	fine-strand without wire end ferrule	0.2-6 mm ² (24-10 AWG)
	rigid	
Stripping length	8 mm (0.31 in)	
Environmental Data		
Ambient temperature range	operation	-40...+70 °C
	rated load	-40...+60 °C
	storage	-40...+85 °C
Damp heat (cyclic)	(IEC/EN 60068-2-30)	95 % without condensation
Shock (half-sine)	(IEC/EN 60068-2-27)	15 G, 11 ms, 3 axes, 6 faces, 3 times for each face
Vibration (sinusoidal)	(IEC/EN 60068-2-6)	10-500 Hz, 2 G, along X, Y, Z each axis, 60 min. for each axis
Standards		
Product standard	EN 61204-3	
Low Voltage Directive	2006/95/EC	
EMC directive	2004/108/EC	
RoHS directive	2002/95/EC	
Electrical safety	EN 60950-1, UL 60950-1, UL 508, EN 61558-1, EN 61558-2-17; EN 60204-1	

Electromagnetic Compatibility		
Interference immunity to:		IEC/EN 61000-6-2
Electrostatic discharge	IEC/EN 61000-4-2	Level 4 (air discharge 15 kV / contact discharge 8 kV)
Radiated, radio-frequency, electromagnetic field IEC/EN	IEC/EN 61000-4-3	Level 3 (10 V/m)
Electrical fast transient/burst	IEC/EN 61000-4-4	Level 4 (4 kV / 2.5 kHz)
Surge	IEC/EN 61000-4-5	L-L Level 3 (2 kV) / L-PE Level 4 (4 kV)
Conducted disturbances, induced by radio-frequency fields	IEC/EN 61000-4-6	Level 3 (10 Vrms)
Power frequency magnetic fields	IEC/EN 61000-4-6	Level 4 (30 A/m)
Voltage dips, short interruptions and voltage variations	IEC/EN 61000-4-6	dip: >95 % 10 ms / >30 % 500 ms interruptions: >95 % 5000 ms
Interference emission		IEC/EN 61000-6-3
High-frequency radiated	IEC/CISPR 22, EN 55022	Class B
IEC/CISPR 22, EN 55022	IEC/CISPR 22, EN 55022	Class B
Limits for harmonic current emissions		Class D

Electrical and Electronic Wire & Cable • Enterprise Cabling & Security Solutions • OEM Supply – Fasteners
 Anixter Inc. World Headquarters • 2301 Patriot Boulevard, Glenview, IL 60026-8020 • 1.800.ANIXTER • 224.521.8000 • anixter.com

Anixter is a leading global distributor of enterprise cabling and security solutions, electrical and electronic wire and cable, and OEM supply – fasteners and other small parts.

We reduce risk, complexity and cost from our customers' purchasing decisions, business processes and supply chains.

Anixter does not manufacture these products. Any product warranties are provided by the applicable manufacturers. Data and suggestions made are not to be construed as recommendations to purchase or as authorizations to use any products in violation of any law or regulation. TO THE FULLEST EXTENT PERMITTED BY LAW, ANIXTER DISCLAIMS ALL WARRANTIES, EITHER EXPRESS OR IMPLIED. ANIXTER MAKES NO WARRANTY OR REPRESENTATION, EXPRESS OR IMPLIED, ABOUT THE ACCURACY OR COMPLETENESS OF ANY INFORMATION PROVIDED.