

## Anixter Level 2 for Industrial Network Environments

Power Supplies: 24V 20 A Three Phase



Anixter Item #	Product Description
L2-24V-20A-3P	DIN Rail Mount Power Supply, Three Phase, 24 VDC / 20 A

Input Circuit	
Rated input voltage U	3 x 400-500 V AC
Input voltage range	340-575 V AC 480-820 V DC
Frequency range AC	47-63 Hz
Typical input current	1.1 A
Typical power consumption	538 W
Inrush current limiting	20 A
Internal input fuse	T3.15 A / 500 V AC
Power factor correction (PFC)	< 3.5 mA

Indication of Operational States:		
Output voltage	Green LED	OUTPUT OK: V: output voltage OK
	Red LED	OUTPUT LOW: V: output voltage too low
Output Circuit		
Rated output voltage	24 V DC	
Tolerance of the output voltage	0...+1 %	
Adjustment range of the output voltage	22.5-28.5 V DC	
Rated output power	480 W	
Rated output current I	20 A	
Signaling contact for output voltage OK	solid-state (max. 60 VDC, 0.3 A)	
Minimum fuse rating to achieve short-circuit protection	M 60 V DC, m 0.3 A fast-acting	
Output circuit - No-load, overload and short-circuit behavior:		
Efficiency	typ. 90%	
Duty time	100%	
Dimensions (W x H x D)	150 x 124 x 118.8 mm [5.91 x 4.88 x 4.68 in]	
Weight	1.657 kg (3.653 lb)	
Material of housing	Metal	
Mounting	DIN rail (IEC/EN 60715), snap-on mounting without any tool	
Mounting position	horizontal	
Degree of protection housing / terminals	IP20 / IP20	
Electrical connection - input circuit / output circuit:		
Wire size fine-strand with wire end ferrule	fine-strand with wire end ferrule	0.2-4 mm <sup>2</sup> (24-11 AWG)
	fine-strand without wire end ferrule	0.2-6 mm <sup>2</sup> (24-10 AWG)
	rigid	0.2-6 mm <sup>2</sup> (24-10 AWG)
Stripping length	8 mm (0.31 in)	

Environmental Data		
<b>Ambient temperature range</b>	operation	-30...+70 °C
	rated load	-30...+70 °C
	storage	-40...+85 °C
<b>Damp heat (cyclic)</b>	(IEC/EN 60068-2-30)	95 % without condensation
<b>Shock (half-sine)</b>	(IEC/EN 60068-2-27)	Half sine wave, 15G, 11 ms, 3 axes, 6 Faces, 3 times for each face
<b>Vibration (sinusoidal)</b>	(IEC/EN 60068-2-6)	10-500 Hz, 2G, each along X, Y, Z axes 6 min / cycle
Standards		
<b>Product standard</b>		EN 61204-3
<b>Low Voltage Directive</b>		2006/95/EN
<b>EMC directive</b>		2004/108/EN
<b>RoHS directive</b>		2002/95/EN
<b>Electrical safety</b>		EN 60950-1, UL 60950-1, UL 508, EN 61558-1, EN 61558-2-17; EN 60204-1
Electromagnetic Compatibility		
<b>Interference immunity to:</b>		IEC/EN 61000-6-2
<b>Electrostatic discharge</b>	IEC/EN 61000-4-2	Level 4 (air discharge 15 kV / contact discharge 8 kV)
<b>Radiated, radio-frequency, electromagnetic field IEC/EN</b>	IEC/EN 61000-4-3	Level 3 (10 V/m)
<b>Electrical fast transient/burst</b>	IEC/EN 61000-4-4	Level 4 (4 kV / 5 kHz)
<b>Surge</b>	IEC/EN 61000-4-5	L-L Level 3 (2 kV) / L-PE Level 4 (4 kV)
<b>Conducted disturbances, induced by radio-frequency fields</b>	IEC/EN 61000-4-6	Level 3 (10 Vrms)



<b>Power frequency magnetic fields</b>	IEC/EN 61000-4-6	Level 4 (30 A/m)
<b>Voltage dips, short interruptions and voltage variations</b>	IEC/EN 61000-4-6	dips: >95 % 0.5 ms / >30 % 0.5 ms interruptions: >95 % 250 ms
<b>Interference emission</b>	IEC/EN 61000-6-3	
<b>High-frequency radiated</b>	IEC/CISPR 22, EN 55022	Class B
<b>IEC/CISPR 22, EN 55022</b>	IEC/CISPR 22, EN 55022	Class B
<b>Limits for harmonic current emissions</b>	Class A	

Electrical and Electronic Wire & Cable • Enterprise Cabling & Security Solutions • OEM Supply – Fasteners  
 Anixter Inc. World Headquarters • 2301 Patriot Boulevard, Glenview, IL 60026-8020 • 1.800.ANIXTER • 224.521.8000 • anixter.com

Anixter is a leading global distributor of enterprise cabling and security solutions, electrical and electronic wire and cable, and OEM supply – fasteners and other small parts.  
 We reduce risk, complexity and cost from our customers' purchasing decisions, business processes and supply chains.

Anixter does not manufacture these products. Any product warranties are provided by the applicable manufacturers. Data and suggestions made are not to be construed as recommendations to purchase or as authorizations to use any products in violation of any law or regulation. TO THE FULLEST EXTENT PERMITTED BY LAW, ANIXTER DISCLAIMS ALL WARRANTIES, EITHER EXPRESS OR IMPLIED. ANIXTER MAKES NO WARRANTY OR REPRESENTATION, EXPRESS OR IMPLIED, ABOUT THE ACCURACY OR COMPLETENESS OF ANY INFORMATION PROVIDED.