



195PQMR-CR  
QMA Male Right Angle for CNT-195 braided cable

## General Specifications

Interface	QMA Male
Body Style	Right angle
Brand	CNT®


## Electrical Specifications

Operating Frequency Band	0 – 6000 MHz
Cable Impedance	50 ohm
Connector Impedance	50 ohm
RF Operating Voltage, maximum (vrms)	353.00 V
dc Test Voltage	1000 V
Outer Contact Resistance, maximum	2.50 mOhm
Inner Contact Resistance, maximum	3.00 mOhm
Insulation Resistance, minimum	5000 MOhm
Average Power	150.0 W @ 900 MHz
Peak Power, maximum	2.50 kW
Insertion Loss, typical	0.05 dB

195PQMR-CR



## Outline Drawing



## Mechanical Specifications

Outer Contact Plating	Trimetal
Inner Contact Plating	Gold
Outer Contact Attachment Method	Crimp
Inner Contact Attachment Method	Solder
Interface Durability	100 cycles
Interface Durability Method	IEC 61169-15:9.5
Connector Retention Tensile Force	134 N   30 lbf
Connector Retention Torque	0.17 N-m   0.13 ft lb
Insertion Force	22.00 N   4.95 lbf
Insertion Force Method	IEC 61169-15:9.3.5
Pressurizable	No

## Dimensions

Nominal Size	0.195 in
Height	23.36 mm   0.92 in
Length	17.42 mm   0.69 in
Weight	7.66 g   0.02 lb
Width	10.50 mm   0.41 in

## Environmental Specifications

Operating Temperature	-40 °C to +85 °C (-40 °F to +185 °F)
Storage Temperature	-65 °C to +125 °C (-85 °F to +257 °F)
Water Jetting Test Mating	Mated

195PQMR-CR

POWERED BY



Water Jetting Test Method	IEC 60529:2001, IP65
Mechanical Shock Test Method	IEC 60068-2-27
Climatic Sequence Test Method	IEC 60068-1
Damp Heat Steady State Test Method	IEC 60068-2-3
Thermal Shock Test Method	IEC 60068-2-14
Vibration Test Method	IEC 60068-2-6
Corrosion Test Method	IEC 60068-2-11

## Standard Conditions

Attenuation, Ambient Temperature	20 °C   68 °F
Average Power, Ambient Temperature	40 °C   104 °F
Average Power, Inner Conductor Temperature	100 °C   212 °F

## Return Loss/VSWR

Frequency Band	VSWR	Return Loss (dB)
0–3000 MHz	1.17	22.10

## Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant by Exemption
China RoHS SJ/T 11364-2006	Above Maximum Concentration Value (MCV)
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system



## \* Footnotes

Insertion Loss, typical    0.05v<sup>-</sup>freq (GHz) (not applicable for elliptical waveguide)