

Anixter Level 3 for Industrial Network Environments

Industrial Ethernet Connector: Cat 6A Solid/Stranded, Unshielded/Shielded M12



L3-M-6-M12-SHD-STR	Cat 6A M12 field plug, X-coded, Straight, Solid/Stranded, Unshielded/Shielded
---------------------------	---

General Data	
Dimensions	16.8 x 52 mm
Shield	Yes
Cable Diameter	5.0 to 9.7mm
Conductor	
Solid	0.40 - 0.64 mm AWG 24 - AWG 22
Stranded	0.48 - 0.76 mm AWG 26/7 - AWG 22/7
Transmission Performance	
Category	Cat 6a
Application:	10/100/1000Mbit Ethernet, 10Gig at 55 meters
Material	
Connector Housing	Zinc Die cast, nickel plated
Contact	Gold plating over nickel

Climatic Properties	
Temperature Range	-40 ° to +85 °c
Ingress Protection	IP67
Electrical Properties	
Current carrying capacity at 40 °C	0.5 A
Rated Voltage	50 V AV / 60 V DC

Electrical and Electronic Wire & Cable • Enterprise Cabling & Security Solutions • OEM Supply – Fasteners
Anixter Inc. World Headquarters • 2301 Patriot Boulevard, Glenview, IL 60026-8020 • 1.800.ANIXTER • 224.521.8000 • anixter.com

Anixter is a leading global distributor of enterprise cabling and security solutions, electrical and electronic wire and cable, and OEM supply – fasteners and other small parts.

We reduce risk, complexity and cost from our customers' purchasing decisions, business processes and supply chains.

Anixter does not manufacture these products. Any product warranties are provided by the applicable manufacturers. Data and suggestions made are not to be construed as recommendations

to purchase or as authorizations to use any products in violation of any law or regulation. TO THE FULLEST EXTENT PERMITTED BY LAW,
ANIXTER DISCLAIMS ALL WARRANTIES, EITHER EXPRESS OR IMPLIED. ANIXTER MAKES NO WARRANTY OR REPRESENTATION, EXPRESS OR IMPLIED,
ABOUT THE ACCURACY OR COMPLETENESS OF ANY INFORMATION PROVIDED.