





RACK SYSTEMS	
<b>L</b> Two-Post Rack Systems	
<i>High strength, fixed two-post racks with small footprints.</i>	
48353-703	Universal Rack, 7'H (2.1 m) x 19"EIA x 15"D (381 mm), 45U, UL Listed, Supports 1500 lb (680 kg), Black
55053-703	Standard Rack, 7'H (2.1 m) x 19"EIA x 15"D (381 mm), 45U, UL Listed, Supports 1000 lb (453.6 kg), Black
66383-703	Standard Rack, 7'H (2.1 m) x 23"W x 18"D (381 mm), 45U, UL Listed, Supports 1000 lb (453.6 kg), Black
<i>Other heights, styles and finishes available.</i>	
Shelves and Trays for 2-Post Rack Systems	
10758-701	Small Peripheral Shelf, 2U x 19"EIA x 10"D (254 mm), Supports 50 lb (22.7 kg)
11054-719	26" Deep Shelf, 5U x 19"EIA x 26"D (660 mm), Supports 150 lb (68.0 kg)
11164-719	Heavy-Duty Equipment Shelf, 5U x 19"EIA x 20"D (504 mm), Supports 200 lb (90.7 kg)
11231-719	Double-Sided Vented Shelf, 4U x 19"EIA x 21.75"D (552 mm), Supports 100 lb (45.4 kg)
11245-719	Adjustable Monitor Shelf, 3U x 19"EIA x 18"D (460 mm), Supports 110 lb (49.9 kg)
11359-719	Low Profile Shelf, Vented, 2U x 19"EIA x 20"D (504 mm), Supports 60 lb (27.2 kg)
13082-719	Lockable Storage Drawer, 2U x 19"EIA x 20"D (510 mm), Supports 100 lb (45.4 kg)
40074-700	Single-Sided Shelf, 3U x 19"EIA x 15"D (380 mm), Supports 50 lb (22.7 kg)
40117-719	Single-Sided Vented Shelf, 3U x 19"EIA x 15"D (380 mm), Supports 50 lb (22.7 kg)
40108-719	Double-Sided Shelf, 4U x 19"EIA x 21.75"D (552.5 mm), Supports 100 lb (45.4 kg)
2-Post Rack System Accessories	
10629-119	Raised Floor Rack Support, 10"-16"H (250 mm to 410 mm), 19"W x 15"D (381 mm)
40604-003	Rack Installation Kit, Concrete Floor, (4) 1/2" Thread Components
12091-719	Equipment Tie-Down Bracket, 19"EIA, for Seismic Areas
12752-719	anyServer Bracket, 2U x 19"EIA, 9"-13"D (230 mm - 330 mm), Supports 120 lb (54.4 kg)
Seismic Frame® Two-Post Rack (not shown)	
<i>NEBS Zone 4 with 1000 lb (453.6 kg) load rating for seismic areas.</i>	
13853-703	7'H (2.1 m) x 19"EIA x 15"D, (380 mm) base, 44U, Supports 1000 lb (453.6 kg), Black
13883-703	7'H (2.1 m) x 23"W x 15"D (380 mm) base, 44U, Supports 1000 lb (453.6 kg), Black
13704-703	Vertical Cabling Section, Double-Sided, 6"W (150 mm)
13702-001	Seismic Frame Two-Post Rack Concrete Floor Anchor Kit
<i>Includes threaded zinc rails. Other styles and finishes available.</i>	
Adjustable QuadraRack® (AOR) (not shown)	
<i>Threaded equipment mounting rails for network switches and shelves.</i>	
15216-703	7'H (2.1 m) x 19"EIA, 22.6"D - 28.5"D (575 mm - 725 mm), 45U, Supports 2000 lb (907.2 kg), Black
15217-703	7'H (2.1 m) x 19"EIA, 29.5"D - 35.4"D (750 mm - 900 mm), 45U, Supports 2000 lb (907.2 kg), Black
15218-703	7'H (2.1 m) x 19"EIA, 36.4"D - 42.3"D (925 mm - 1075 mm), 45U, Supports 2000 lb (907.2 kg), Black
<i>Other sizes and finishes available. Square-punched equipment mounting rails also available.</i>	
Adjustable QuadraRack® (AOR) Accessories	
15255-702	Vented Shelf, 1U x 19"EIA x 20.7"D (526.5 mm), Supports 200 lb (90.7 kg), Black
15255-703	Vented Shelf, 1U x 19"EIA x 27.6"D (701.6 mm), Supports 200 lb (90.7 kg), Black
15255-704	Vented Shelf, 1U x 19"EIA x 34.5"D (876.5 mm), Supports 200 lb (90.7 kg), Black
15235-705	Equipment Support Rails, 35.4"D - 39.3"D (900 mm - 1000 mm), Supports 200 lb (90.7 kg), Black
15235-706	Equipment Support Rails, 40.3"D - 44.2"D (1025 mm - 1125 mm), Supports 200 lb (90.7 kg), Black
15205-701	Mounting Bracket, for 6"W - 24"W (150 mm - 600 mm), Cable Runway, Black
<i>Other sizes, styles and finishes available.</i>	
<b>J</b> Adjustable Rail ServerRack (ARSR)	
<i>Square-punched equipment mounting rails use cage nuts to mount a variety of server equipment.</i>	
15253-703	7'H (2.1 m) x 19"EIA x 23.6"D (600 mm), 45U, 2200 lb (1000 kg), Black
15254-703	7'H (2.1 m) x 19"EIA x 35.4"D (900 mm), 45U, 2200 lb (1000 kg), Black
<i>Other sizes and finishes available. Threaded equipment mounting rails also available.</i>	
Adjustable Rail ServerRack (ARSR) Accessories	
15270-702	Adjustable Rail ServerRack Side Panel, 7'H x 23.6"D (2.1 m x 600 mm), Black
15285-701	Equipment Support Rails, for 23.6"D (600 mm) Racks
<b>G</b> Velocity® Standard Pack	
<i>Easy to use solution for managing equipment and cabling at the cross-connect.</i>	
57011-703	(1) Standard Rack, 45U x 19"EIA; (1) Velocity Single-Sided Vertical Cable Manager 3.6"W (91 mm); and (1) Rack Installation Kit for Concrete Floors, Black
57012-703	(1) Standard Rack, 45U x 19"EIA; (1) Velocity Double-Sided Vertical Cable Manager 3.6"W (91 mm); and (1) Rack Installation Kit for Concrete Floors, Black
57013-703	(1) Standard Rack, 45U x 19"EIA; (1) Velocity Single-Sided Vertical Cable Manager 6.0"W (150 mm); and (1) Rack Installation Kit for Concrete Floors, Black
57014-703	(1) Standard Rack, 45U x 19"EIA; (1) Velocity Double-Sided Vertical Cable Manager 6.0"W (150 mm); and (1) Rack Installation Kit for Concrete Floors, Black

CABINET & ENCLOSURE SYSTEMS	
<b>A</b> F-Series TeraFrame® Gen 3 Cabinet System	
<i>Stores servers in enterprise data centers, computer rooms and network facilities.</i>	
FF1N-113B-C42-B	84.6"H x 23.6"W x 43.3"D (2149 mm x 600 mm x 1100 mm), 45U, 19"EIA, 6-Slide Supports 3000 lb (1360 kg), Black
FF1U-113B-C42-B	84.6"H x 23.6"W x 47.2"D (2149 mm x 600 mm x 1200 mm), 45U, 19"EIA, 6-Slide Supports 3000 lb (1360 kg), Black
FF2N-113B-C42-B	84.6"H x 27.6"W x 43.3"D (2149 mm x 700 mm x 1100 mm), 45U, 19"EIA, 6-Slide Supports 3000 lb (1360 kg), Black
FF2U-113B-C42-B	84.6"H x 27.6"W x 47.2"D (2149 mm x 700 mm x 1200 mm), 45U, 19"EIA, 6-Slide Supports 3000 lb (1360 kg), Black
FF3U-113B-C42-B	84.6"H x 31.5"W x 47.2"D (2149 mm x 800 mm x 1200 mm), 45U, 19"EIA, 6-Slide Supports 3000 lb (1360 kg), Black
<i>Cabinet includes top panel, two side panels and perforated front and rear doors. Order thermal, power and cable management accessories separately. Other options and finishes available.</i>	
<b>S</b> F-Series TeraFrame® Gen 3 Cabinet System with Vertical Exhaust Duct	
<i>Isolate and remove hot exhaust air from the cabinet to an overhead return.</i>	
FF1U-111B-C52-B	84.6"H x 23.6"W x 47.2"D (2149 mm x 600 mm x 1200 mm), 45U, with 20" - 34"H (508 mm - 863 mm) Vertical Exhaust Duct, Supports 3000 lb (1360 kg), Black
FF1U-111B-C62-B	84.6"H x 23.6"W x 47.2"D (2149 mm x 600 mm x 1200 mm), 45U, with 34"- 60"H (863 mm - 1523 mm) Vertical Exhaust Duct, Supports 3000 lb (1360 kg), Black
FF2U-111B-C52-B	84.6"H x 27.6"W x 47.2"D (2149 mm x 700 mm x 1200 mm), 45U, with 20"-34"H (508 mm - 863 mm) Vertical Exhaust Duct, Supports 3000 lb (1360 kg)
FF2U-111B-C62-B	84.6"H x 27.6"W x 47.2"D (2149 mm x 700 mm x 1200 mm), 45U, with 34"-60"H (863 mm - 1523 mm) Vertical Exhaust Duct, Supports 3000 lb (1360 kg)
<i>Cabinet includes top panel with duct, two side panels, perforated front door and a solid rear door. Order thermal, power and cable management accessories separately. Other finishes and options available.</i>	
<b>D</b> N-Series TeraFrame® Gen 3 Network Cabinet	
NF1U-113C-C42-1	83.5"H x 31.5"W x 47.2"D (2122 mm x 800 mm x 1200 mm), 45U, 19"EIA, Side Airflow, Supports 2500 lb (1134 kg), Black
NF5U-113C-C42-1	83.5"H x 40.0"W x 47.2"D (2122 mm x 1016 mm x 1200 mm), 45U, 19"EIA, Side Airflow, Supports 2500 lb (1134 kg), Black
NF7U-113C-C42-1	83.5"H x 31.5"W x 47.2"D (2122 mm x 800 mm x 1200 mm), 45U, 19"EIA, Front Airflow, Supports 2500 lb (1134 kg), Black
NF8U-113C-C42-1	83.5"H x 40.0"W x 47.2"D (2122 mm x 1016 mm x 1200 mm), 45U, 19"EIA, Front Airflow, Supports 2500 lb (1134 kg), Black
<i>Cabinet includes top panel with duct, two side panels, perforated front and rear doors and internal side or front airflow air dams for a network switch. Other finishes and options available.</i>	
<b>U</b> N-Series TeraFrame® Gen 3 Network Cabinet with Vertical Exhaust Duct	
NF7U-115C-C52-1	83.5"H x 31.5"W x 47.2"D (2122 mm x 800 mm x 1200 mm), 45U, 19"EIA, Front Airflow, 20"-34" (508 mm-863 mm) Vertical Exhaust Duct, Supports 2500 lb (1134 kg), Black
NF5U-114C-C62-1	83.5"H x 40.0"W x 47.2"D (2122 mm x 1016 mm x 1200 mm), 45U, 19"EIA, Side Airflow, 34"-60" (863 mm-1523 mm) Vertical Exhaust Duct, Supports 2500 lb (1134 kg), Black
<i>Cabinet includes top panel with duct, two side panels, perforated front and rear doors and internal side or front airflow air dams for a network switch. Other finishes and options available.</i>	
<b>B</b> GF-Series GlobalFrame® Gen 2 Cabinet System	
<i>Industry Standard, cost effective, general purpose cabinet for computer and equipment rooms.</i>	
GF-1A220-CB	79.4"H x 23.6"W x 39.4"D (2016 mm x 600 mm x 1000 mm), 42U, 19"EIA, 6-Slide Supports 3000 lb (1360 kg), Black
GF-1A420-CB	79.4"H x 23.6"W x 47.2"D (2016 mm x 600 mm x 1200 mm), 42U, 19"EIA, 6-Slide Supports 3000 lb (1360 kg), Black
GF-1C120-CB	79.4"H x 31.5"W x 31.5"D (2016 mm x 800 mm x 800 mm), 42U, 19"EIA, 6-Slide Supports 3000 lb (1360 kg), Black
GF-1C220-CB	79.4"H x 31.5"W x 39.4"D (2016 mm x 800 mm x 1000 mm), 42U, 19"EIA, 6-Slide Supports 3000 lb (1360 kg), Black
GF-1C420-CB	79.4"H x 31.5"W x 47.2"D (2016 mm x 800 mm x 1200 mm), 42U, 19"EIA, 6-Slide Supports 3000 lb (1360 kg), Black
<i>Cabinet includes top panel, two side panels, perforated front and rear doors and casters. Order thermal, power and cable management accessories separately. Other options and finishes available.</i>	
<b>T</b> GF-Series GlobalFrame® Gen 2 Cabinet System with Vertical Exhaust Duct	
<i>Isolate and remove hot exhaust air from the cabinet to an overhead return. Other sizes and finishes available.</i>	
GF-1A421-CB	79.4"H x 23.6"W x 47.2"D (2016 mm x 600 mm x 1200 mm), 42U, 19"EIA, 20"-34" H (508 mm - 863 mm) Vertical Exhaust Duct, Supports 3000 lb (1360 kg), Black
GF-1A422-CB	79.4"H x 23.6"W x 47.2"D (2016 mm x 600 mm x 1200 mm), 42U, 19"EIA, 34"-60" H (863 mm - 1523 mm) Vertical Exhaust Duct, Supports 3000 lb (1360 kg), Black
<i>Cabinet includes top panel with duct, two side panels, perforated front door, solid rear door, bottom panel and casters. Order thermal, power and cable management accessories separately.</i>	

CABINET & ENCLOSURE SYSTEMS	
<b>C</b> M-Series MegaFrame® Cabinet System	
<i>General purpose, light weight aluminum cabinet delivers partially assembled for easier handling.</i>	
M1033-741	84"H x 27.3"W x 32.1"D (2130 mm x 694 mm x 816 mm), 45U, 19"EIA Supports 2000 lb (907.2 kg), Black
M1053-741	84"H x 27.3"W x 38.1"D (2130 mm x 694 mm x 968 mm), 45U, 19"EIA Supports 2000 lb (907.2 kg), Black
M1043-741	84"H x 27.3"W x 41.1"D (2130 mm x 694 mm x 1045 mm), 45U, 19"EIA Supports 2000 lb (907.2 kg), Black
<i>Cabinet includes top panel, two side panels and perforated front and rear doors. Order thermal, power and cable management accessories separately. Other options and finishes available.</i>	
Seismic Frame® Cabinet System (not shown)	
<i>Steel inner-frame; Rated Zone 4 compliant to BellCore GR-63-CORE for NEBS, Section 4.4.1.1</i>	
11972-742	84"H x 27.3"W x 38.1"D (2130 mm x 694 mm x 968 mm), 43U, 19"EIA Supports 800 lb (362.9 kg), Black
<i>Cabinet includes top panel, two side panels and perforated front and rear doors. Order thermal, power and cable management accessories separately. Other options and finishes available.</i>	
Thermal Management Accessories or Cabinet & Enclosure Systems	
<i>CPI thermal management accessories prevent re-circulation of air within the cabinet.</i>	
39085-C03	Air Dam Kit for 45U x 23.6"W (600 mm) F-Series TeraFrame Gen 3 Cabinet
39085-C00	Air Dam Kit for 42U x 23.6"W (600 mm) GF-Series GlobalFrame Gen 2 Cabinet
39132-C00	Bottom Panel for 23.6"W (600 mm) F-Series Gen 3 TeraFrame or GF-Series Gen 2 GlobalFrame Cabinets
13336-710	Air Dam Kit for M-Series MegaFrame Cabinet
39133-001	Equipment Rail Grommet Kit for 27.6"W (700 mm) or 31.5"W (800 mm) GF-Series GlobalFrame Gen 2 Cabinet
34537-000	Snap-In Filler Panel, 1U x 19"EIA, Black
34538-000	Snap-In Filler Panel, 2U x 19"EIA, Black
<i>Add Air Dam Kit/Rail Seal Kit, Bottom Panel, Equipment Rail Grommet Kit and Snap-In Filler Panels to cabinets to block airflow around rack-mount equipment. Other sizes and finishes available.</i>	
Shelves for Cabinet & Enclosure Systems	
13517-701	Rack-Mount Cable Shelf, 1U x 19"EIA
11913-719	Sliding Vented Shelf, 2U x 19"EIA, 32"D (810mm), Supports 160 lb (72.6 kg)
13083-719	Lockable Storage Drawer, 3U x 19"EIA x 20"D (510 mm), Supports 100 lb (45.4 kg)
12700-719	Extra Heavy-Duty Sliding Shelf, 2U x 19"EIA, 26"D (660 mm), Supports 300 lb (136.1 kg)
12610-719	Low Profile Fixed Vented Shelf, 1U x 19"EIA, 20" - 36" D (510 mm - 910 mm), Supports 100 lb (45.4 kg)
Casters for Cabinet & Enclosure Systems	
13203-001	Caster Kit for MegaFrame Cabinet
<i>Other accessory options available.</i>	
Installation Hardware for Cabinet & Enclosure Systems	
12637-001	Equipment Mounting Hardware, M6, Pack of 25
12639-001	Equipment Mounting Hardware, #12-24, Pack of 25
40604-003	Universal Rack/Cabinet Installation Kit, Concrete Floor, 1/2" Hardware
Keyboard, Video and Mouse (KVM) Switches)	
<i>Share a common set of peripherals with all rack-mount equipment and /or access equipment remotely over an IP connection through a KVM switch. Contact CPI Technical Support for configuration assistance.</i>	
Electronic Locking System (ELS)	
<i>Upgrade to electronic locks on F-Series TeraFrame Gen 3 and GF-Series GlobalFrame Gen 2 Cabinet for automated and remote access control. Contact CPI Technical Support for ordering assistance.</i>	
Power Distribution Units (PDUs)	
<i>Single-phase and three-phase, Basic, Monitored and Switched outlet vertical PDUs are available for all cabinet systems. Contact CPI Technical Support for configuration assistance.</i>	
Environmental Monitoring Solutions	
<i>Provide critical automated environmental monitoring, logging &amp; reporting within cabinets and equipment rooms. Contact CPI Technical Support for configuration assistance.</i>	
<b>E</b> Aisle Containment Solutions	
<i>Enclose or duct the hot or cold aisle between adjacent rows of F-Series, N-Series and GF-Series Cabinets. Contact CPI Technical Support for configuration assistance.</i>	

WALL-MOUNT SYSTEMS	
<b>O</b> CUBE-IT PLUS® Cabinet System	
<i>Wall-mounted equipment storage with easy access to the rear of equipment. 60"H (1520 mm) and 72"H (1830 mm) are wall mounted and floor supported. Other sizes and finishes available.</i>	
11890-724	24"H (610 mm) x 19"EIA x 18"D (460 mm), 12U, Supports 200 lb (90.7 kg), Black
11840-724	24"H (610 mm) x 19"EIA x 24"D (610 mm), 12U, Supports 200 lb (90.7 kg), Black
11890-736	36"H (910 mm) x 19"EIA x 18"D (460 mm), 18U, Supports 200 lb (90.7 kg), Black
11840-736	36"H (910 mm) x 19"EIA x 24"D (610 mm), 18U, Supports 200 lb (90.7 kg), Black
11890-748	48"H (1220 mm) x 19"EIA x 18"D (460 mm), 26U, Supports 200 lb (90.7 kg), Black
11840-748	48"H (1220 mm) x 19"EIA x 24"D (610 mm), 26U, Supports 200 lb (90.7 kg), Black
13492-760	60"H (1520 mm) x 19"EIA x 24"D (610 mm), 38U, Supports 1000 lb (453.6 kg), Black
13493-760	60"H (1520 mm) x 19"EIA x 30"D (760 mm), 33U, Supports 1000 lb (453.6 kg), Black
13492-772	72"H (1830 mm) x 19"EIA x 24"D (610 mm), 40U, Supports 1000 lb (453.6 kg), Black
13493-772	72"H (1830 mm) x 19"EIA x 30"D (760 mm), 40U, Supports 1000 lb (453.6 kg), Black
CUBE-IT PLUS® Cabinet System Accessories	
12803-701	Light for CUBE-IT, 115 VAC, 8 Watts, 6'L cord with NEMA 5-15P plug
12804-701	Fan Kit, 115 VAC, 100 CFM, Black
12805-701	Filter Kit for Fan
12796-501	45" Mounting Bracket, 3U, for back of cabinet
13285-501	90" Mounting Bracket, 2U, for back of cabinet
13485-760	Vertical Cable Manager for 60"H (1520 mm) Cabinet
13485-772	Vertical Cable Manager for 72"H (1830 mm) Cabinet
<i>Other Cube-IT cabinets accessories available.</i>	
<b>P</b> ThinLine II Wall-Mount Cabinet System	
<i>Space saving wall-mounted cabinet. Color is black. Other finishes available.</i>	
13050-711	26"H x 26"W x 5"D (660 mm x 660 mm x 130 mm), 2U, Supports 100 lb (45.4 kg)
13050-712	26"H x 26"W x 8.5"D (660 mm x 660 mm x 216 mm), 4U, Supports 100 lb (45.4 kg)
13050-713	26"H x 26"W x 12"D (660 mm x 660 mm x 300 mm), 6U, Supports 100 lb (45.4 kg)
13050-721	36"H x 26"W x 5"D (910 mm x 660 mm x 130 mm), 2U, Supports 100 lb (45.4 kg)
13050-722	36"H x 26"W x 8.5"D (910 mm x 660 mm x 216 mm), 4U, Supports 100 lb (45.4 kg)
13050-723	36"H x 26"W x 12"D (910 mm x 660 mm x 300 mm), 6U, Supports 100 lb (45.4 kg)
ThinLine II Wall-Mount Cabinet System Accessories	
13051-001	Intelligent Fan Kit, 4U & 6U Cabinet
13051-002	Intelligent Fan Kit, 2U Cabinet
Fixed Wall-Mount Equipment Rack (not shown)	
11960-718	27.4"H (696 mm) x 19"EIA x 18"D (460 mm), 12U, Supports 200 lb (90.7 kg)
11961-718	41.4"H (1052 mm) x 19"EIA x 18"D (460 mm), 20U, Supports 200 lb (90.7 kg)
11962-718	76.4"H (1941 mm) x 19"EIA x 18"D (460 mm), 40U, Supports 200 lb (90.7 kg)
<i>Color is Black. Other finishes available. 12" Deep Rack (-X12), 6" Deep Rack (-X06).</i>	
<b>N</b> Standard Swing Gate Rack	
11790-718	29.1" (739 mm) x 19"EIA x 18"D (460 mm), 12U, Supports 100 lb (45.4 kg)
11791-718	43.1" (1095 mm) x 19"EIA x 18"D (460 mm), 20U, Supports 100 lb (45.4 kg)
11792-718	78.1"H (1984 mm) x 19"EIA x 18"D (460 mm), 40U, Supports 100 lb (45.4 kg)
<i>Color is Black. Other finishes available. 12" Deep Rack (-X12), 25" Deep Rack (-X25). 23"W also available.</i>	
Heavy-Duty Wall-Mount Equipment Rack (not shown)	
15320-718	41.2" (1046 mm) x 19"EIA x 18"D (460 mm), 20U, Supports 350 lb (158.8 kg)
15321-718	76.2" (1935 mm) x 19"EIA x 18"D (460 mm), 40U, Supports 350 lb (158.8 kg)
<i>Color is Black. Other finishes available. 24" Deep Rack (-X24).</i>	
EasySwing Wall-Mount Rack (not shown)	
<i>Easy to ship, inventory and install — ships flat, folds open to mount on the wall.</i>	
13602-708	24.5"H (622 mm) x 19"EIA x 8"D (200 mm), 11U, Supports 85 lb (38.6 kg), Black
13604-708	38.5"H (978 mm) x 19"EIA x 8"D (200 mm), 19U, Supports 85 lb (38.6 kg), Black
13608-712	51.5"H (1308 mm) x 19"EIA x 12"D (300 mm), 26U, Supports 85 lb (38.6 kg), Black
<i>Other finishes available. 12" Deep Rack (-X12), 18" Deep Rack (-X18) and 25" Deep Rack (-X25).</i>	
Universal Swing Gate Rack (not shown)	
<i>Full-feature swing gate rack with built-in cable management capabilities. Other finishes available.</i>	
11347-719	40.4"H (1026 mm) x 19"EIA x 12"D (300 mm), 20U, Supports 150 lb (68.0 kg), Black
11348-719	40.4"H (1026 mm) x 19"EIA x 18"D (460 mm), 20U, Supports 150 lb (68.0 kg), Black
Wall-Mount Rack System Accessories	
11799-001	Vertical Cable Management