

# **BasicPatch**

## **Cat 5e FTP RJ45 patch cords**

### **Technical Data Sheet**

**Patent Pending**



#### **Cat 5e RJ 45 Patch Cords :**

**PatchSee** RJ 45 Patch Cords are designed, and individual tested for connecting the network equipment to patch panel and network user outlet. They are warranted for cat 5e TIA/EIA-568-B-2.1 June 2002 Channel test on a Permanent Link certified for transmission frequencies of up to 100 MHz.

#### **PatchSee Concept and main characteristics**

- Light identification by plastic optical fiber,
- Many lengths 2 feet (0.6 m) up to 16 feet (4.9 m) for patch panel and terminal link,
- Color cable: Black with white marking,
- Color boot: Grey with white marking,
- Movable color clip, 16 colors available,
- Packaging: boxes of 12 pieces, depending of the length,
- Available in cross patch cord,
- Marking on the boot: length and P/N,
- Unique serial number marking on the cable,
- Individual tested: each Patch Cord is individual tested (Return Loss, Attenuation, NEXT, etc...) and all the reports tests are archiving on computer database.

## Technical Data Sheet

### Construction

<b>Number of pairs</b>	4
<b>Conductor</b>	Stranded bare copper wire
<b>Gage</b>	26 AWG
<b>Insulation</b>	Foam Skin Polyethylene
<b>Pair screen</b>	Al-laminated metal foil
<b>Optical wave guide</b>	2 POF 0.5 mm
<b>Drain</b>	Stranded drain wire tinned
<b>Jacket</b>	PVC Black with white printing
<b>Overall diameter</b>	5.8 mm
<b>Plug housing</b>	UL 1863 Polycarbonate
<b>Contacts</b>	Moved contacts
<b>Contact Plating</b>	50 $\mu$ inches gold minimum (1.2 $\mu$ m)
<b>Shielding</b>	Tin-plated

### Mechanical Properties of the cable

Fire Propagation Test	Temperature range During operation	Fire load	Bending radius
UL 444 VW 1 Flame test	-20°C up to +75°C	372 MJ/km	>25 mm without load

### Electrical Properties of the cable (at 20°C +/- 5°C)

DC loop resistance	Insulation resistance (500V)	Capacitance at 800 Hz	Impedance 1-100MHz	Impedance 100-250MHz	Propagation delay	Test voltage (DC, 1 min)
< 340 $\Omega$ /km	> 2000 M $\Omega$ *km	Nom. 43nF/km	100 +/- 15 $\Omega$	NA	< 427 ns/100m	1000 V