

111-95149

Article Number: 111-95149

Stainless Steel Tie, 14.3" Long, 607lb Tensile Strength, SS316, Metal, 50/pkg



Base Data

Local Order Number 111-95149

Type MBT14XH

Color Metal (ML)

Features and Benefits

- 316 grade stainless steel offers excellent resistance to salt spray, corrosion, weather and chemical resistance.
- Ball bearing locking mechanism assures high tensile strength and easy insertion.

Product Description HellermannTyton's stainless steel ties are designed with a ball bearing locking mechanism to assure high tensile strength and easy insertion when securing hoses, cables, pipes and more. Available in 304 or 316 grades of stainless steel, providing protection when used in corrosive environments, fire resistance and temperature extremes.

Fixation Method (FF) None

Identification Plate Position none

Releasable Closure (Yes/No) No

Tie Closure ball bearing lock

Variant No Serration

Short Description Stainless Steel Tie, 14.3" Long, 607lb Tensile Strength, SS316, Metal, 50/pkg

Product Dimensions

Minimum Tensile Strength (imperial) 607.0 lbs

Minimum Tensile Strength (N) 2700.0 N

Length L (imperial) 14.3 "

Length L (metric) 362.0 mm

Width W (imperial) 0.48 "

Width W (metric) 12.3 mm

Bundle Diameter min (imperial) 0.47 "

Bundle Diameter min (metric) 12.0 mm

Bundle Diameter max (imperial) 4.0 "

Bundle Diameter max (metric) 102.0 mm

Thickness T (imperial) 0.01 "

Cable Tie Head Height (Metric) 5.4 mm

Cable Tie Head Length (metric) 14.5 mm

Cable Tie Head Width (metric) 14.6 mm

Cable Tie Head Length (imperial) 0.55 "

Cable Tie Head Width (imperial) 0.57 "

Thickness T (Metric) 0.3 mm

Logistics and Packaging

Quantity per pc
Package Quantity 50
Carton Quantity 1000 Pieces
Weight (Metric) 13.3 kg

Material and Specifications

Material Stainless Steel (SS316)
Material Shortcut SS316
Flammability non-burning
Halogenfree Yes
Operating Temperature -112 °F to +1000 °F (-80 °C to +538 °C)
ROHS Conformity Yes
Certification / Specification BV
GL
ABS