



## CM-L60-B

**Light Duty Chain Mount Base Kit, 16 ft chain**

### Dimensions

Mounting Diameter, maximum	1524.0 mm		60 in
Mounting Diameter, minimum	203.2 mm		8 in
Pipe Outer Diameter	114.3 mm		4 1/2 in
Height	152.4 mm		6.0 in
Length	203.2 mm		8.0 in
Mounting Circumference, maximum	4775.2 mm		188.0 in
Mounting Circumference, minimum	635.0 mm		25.0 in
Weight	17.3 kg		38.1 lb
Width	203.2 mm		8.0 in

### Environmental Specifications

Man Rating	250 lb vertical man load at 15 mph (BWS)
Wind Rating	120 mph (BWS) at 100 ft AGL
Wind Rating Criteria	One 2 ft standard microwave antenna, with radome and stiff arm
Wind Rating Test Method	TIA/EIA-222


### General Specifications

Product Type	Chain mount
Pipe, quantity	0
Chain Length	4.9 m   16.0 ft
Chains, quantity	2
Includes	Chains
Material Type	Hot dip galvanized steel
Package Quantity	1
Sectors, quantity	1

CM-L60-B



## Outline Drawing



## Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system

### \* Footnotes

Man Rating	BWS—Base Wind Speed
Wind Rating	BWS—Base Wind Speed; FBC—Florida Building Code