

111-95338

Article Number: 111-95338

Stainless Steel Tie, 33" Long, 607lb Tensile Strength, SS304, Metal, 50/pkg



Base Data

Local Order Number	111-95338
Type	MBT33X-HS
Color	Metal (ML)
Features and Benefits	• 304 grade stainless steel offers excellent resistance to corrosion, weather and chemical resistance. • Ball bearing locking mechanism assures high tensile strength and easy insertion.
Product Description	HellermannTyton's stainless steel ties are designed with a ball bearing locking mechanism to assure high tensile strength and easy insertion when securing hoses, cables, pipes and more. Available in 304 or 316 grades of stainless steel, providing protection when used in corrosive environments, fire resistance and temperature extremes.
Fixation Method (FF)	None
Identification Plate Position	none
Releasable Closure (Yes/No)	No
Tie Closure	ball bearing lock
Variant	No Serration
Short Description	Stainless Steel Tie, 33" Long, 607lb Tensile Strength, SS304, Metal, 50/pkg

Product Dimensions

Minimum Tensile Strength (imperial)	607.0 lbs
Minimum Tensile Strength (N)	2700.0 N
Length L (imperial)	33.0 "
Length L (metric)	838.0 mm
Width W (imperial)	0.48 "
Width W (metric)	12.3 mm
Bundle Diameter min (imperial)	0.67 "
Bundle Diameter min (metric)	17.0 mm
Bundle Diameter max (imperial)	10.0 "
Bundle Diameter max (metric)	254.0 mm
Thickness T (imperial)	0.01 "
Thickness T (Metric)	0.3 mm

Logistics and Packaging

Quantity per	pc
Package Quantity	50
Carton Quantity	50
Weight (Metric)	24.23 kg

Material and Specifications

Material	Stainless Steel (SS304)
Material Shortcut	SS304
Flammability	non-burning
Halogenfree	Yes
Operating Temperature	-112 °F to +1000 °F (-80 °C to +538 °C)
ROHS Conformity	Yes