

CM-SL30  
Light Duty Stiff Arm Mount, one 8 ft chain

## Dimensions

Mounting Diameter, maximum	762.0 mm		30 in
Mounting Diameter, minimum	203.2 mm		8 in
Height	152.4 mm		6.0 in
Length	1168.4 mm		46.0 in
Mounting Circumference, maximum	2392.7 mm		94.2 in
Mounting Circumference, minimum	635.0 mm		25.0 in
Weight	16.8 kg		37.0 lb
Width	203.2 mm		8.0 in

## General Specifications


Product Type	Stiff arm mount
Chain Length	2.4 m   8.0 ft
Chains, quantity	1
Includes	Chains   Stiff arm attachment
Material Type	Hot dip galvanized steel
Package Quantity	1
Stand-off Distance	1219.2 mm   48.0 in

CM-SL30

POWERED BY



## Outline Drawing



## Regulatory Compliance/Certifications

### Agency

ISO 9001:2008

### Classification

Designed, manufactured and/or distributed under this quality management system