



FO42BBS2
FlexTwist™ Flexible Twist for WR42, 17.7–26.5 GHz, with interface types UG-595/U and UG-595/U, 600 mm

Electrical Specifications

Operating Frequency Band	17.7 – 26.5 GHz
Attenuation	0.80 db/ft 2.62 db/m
Average Power	100 W
Peak Power	39.0 kW
VSWR	1.25


General Specifications

Component	Flexible Twist
Waveguide Size	WR42 WG20 R220
Interface	UG-595/U
Interface 2	UG-595/U
Length	600 mm 24 in


Mechanical Specifications

Maximum Twist	510.00 °/m 155.00 °/ft
Minimum Bend Radius, Multiple Bends (E Plane)	38.00 mm 1.50 in
Minimum Bend Radius, Multiple Bends (H Plane)	76.00 mm 3.00 in
Pressurization, maximum	45 psi 310 kPa


Component



Interface



Interface 2



Regulatory Compliance/Certifications

Agency RoHS 2011/65/EU China RoHS SJ/T 11364-2006 ISO 9001:2008	Classification Compliant by Exemption Above Maximum Concentration Value (MCV) Designed, manufactured and/or distributed under this quality management system
---	--

Product Specifications

COMMScope®

F042BBS2

POWERED BY

