

47602-24E

Structured Media® Enclosures

Brand Features

Ideal for custom retrofit and remodel applications, the Media Versatile Panel with 3/4" plywood backing allows an open architecture for consolidating low voltage electronics and distribution components for phone, fax/modem, data, home networking, audio, video and home control. The 24" high cold-rolled steel panel with securable door will accommodate a wide variety of Structured Media Distribution Modules by simply removing the grommets and attaching directly to the plywood backing. The sturdy construction is built to industrial-grade standards, and the panel can be surface mounted or recessed in the wall. (Optional mounting brackets may be used for non-standard stud spacing). Ideal for custom retrofit and remodel applications. Available in black powder coat finish.

Item Description

Media Versatile Panel

Technical Information

Dimensional Data

Height: 24 Inch

Width: 14 inch

Depth: 6 Inch

Material Specifications

Enclosure Material: Steel

Gauge of Steel: 18 Gauge

Paint Finish: Powder-Coated

Color: Black

Product Features

Series: Media Versatile

Item: Enclosure and Flush Mount Cover

Height: 24 Inch

Width: 14 inch

Depth: 6 Inch

Gauge of Steel: 18 Gauge

Paint Finish: Powder-Coated

Color: Black

Standards and Certifications: UL

Warranty: 2 Year Limited Plus

Standards and Certifications

UL Listed: Fire and Burglary



Color:



Black

UPC Code: 07847728555

Country of Origin: Mexico - *Eligible for
ARRA funded projects > \$7,443,000



Features and Benefits

- Eight 1 Inch or 1-1/2 Inch conduit fittings on top and bottom facilitate cable entry and routing.
- Wall-Mount or recess. ideal for new installations or retrofits.
- Securable door provides maximum protection from dust and abuse.
- Plywood backing allows open architecture for customizing layout and can accommodate a wide variety of Structured Media Distribution Modules.

SPECIFICATION SUBMITTAL

JOB NAME: <input type="text"/>	CATALOG NUMBERS: <input type="text"/>	
JOB NUMBER: <input type="text"/>	<input type="text"/>	<input type="text"/>

Leviton Manufacturing Co., Inc.

201 North Service Road, Melville, NY 11747

Telephone: 1-800-323-8920 • FAX: 1-800-832-9538 • Tech Line (8:30AM-7:30PM E.S.T. Monday-Friday): 1-800-824-3005

Leviton Manufacturing of Canada, Ltd.

165 Hymus Boulevard, Pointe Claire, Quebec H9R 1E9 • Telephone: 1-800-469-7890 •

FAX: 1-800-824-3005 • www.leviton.com/canada**Leviton S. de R.L. de C.V.**Lago Tana 43, Mexico DF, Mexico CP 11290 • Tel.: (+52)55-5082-1040 • FAX: (+52)5386-1797 • www.leviton.com.mx**Visit our Website at: www.leviton.com**

© 2012-2014 Leviton Manufacturing Co., Inc. All rights reserved. Subject to change without notice.

**Leviton has a global presence.**If you would like to know where your local Leviton office is located please go to: www.leviton.com/international/contacts/

**Buy American Compliant Logo -- The American Recovery And Reinvestment Act of 2009 ("ARRA") provides federal grants and loans for projects throughout the country. Section 1605 of the Act, named the "Buy American" provision, requires that certain materials and manufactured products used in projects funded by the Act be manufactured in the United States. The appearance of the Recovery Act Logo in relation to a Leviton product is only intended to reflect that such product may be used in an ARRA funded project. It does not mean that such product or Leviton is sponsored or endorsed by, or that Leviton receives funds from, the federal government or the Recovery Accountability and Transparency Board. Nothing in Leviton's use of the logo is intended to suggest anything regarding the requirements for funding under ARRA.*