

Product Specifications



F042KHS3

Flexible Twist for WR42, 17.7–26.5 GHz, with interface types PBR220 and PDR220, 900 mm



CHARACTERISTICS

Electrical Specifications

Operating Frequency Band	17.7 – 26.5 GHz
Attenuation	0.80 db/ft 2.62 db/m
Average Power	100 W
Peak Power	39.0 kW
VSWR	1.25

General Specifications

Component	Flexible Twist
Waveguide Size	WR42 WG20 R220
Interface	PBR220
Interface 2	PDR220
Length	900 mm 35 in

Mechanical Specifications

Maximum Twist	510.00 °/m 155.00 °/ft
Minimum Bend Radius, Multiple Bends (E Plane)	38.00 mm 1.50 in
Minimum Bend Radius, Multiple Bends (H Plane)	76.00 mm 3.00 in
Pressurization, maximum	45 psi 310 kPa

Component

Interface

Interface 2


www.commscope.com/andrew

©2011 CommScope, Inc. All rights reserved.
All trademarks identified by ® or ™ are registered trademarks or trademarks, respectively, of CommScope. All specifications are subject to change.
See www.commscope.com/andrew for the most current information.

page 1 of 2
5/2/2011

Product Specifications

F042KHS3



Regulatory Compliance/Certifications

Agency

ISO 9001:2008

Classification

Designed, manufactured and/or distributed under this quality management system