


Anixter Level 2 for Industrial Network Environments

Anixter Part #: L2-06-FTB-OS1-05

6 Fiber  
Riser Rated Cables



Fiber Performance	
Fiber Code	SLX
Industry Standard Designation	Low Water Peak Single-mode ITU-T G.652.D
Core/Cladding Diameter (µm)	9/125
Wavelength (nm)	1310/1550
Maximum Cabled Attenuation (dB/km)	0.5/0.5
Primary Coating Diameter (µm)	245
Secondary Buffer Diameter (µm)	900
Zero Dispersion Slope (ps/nm <sup>2</sup> -km)	0.092
Proof Test Level (kpsi)	100

Installation and Operating Characteristics		
	Installation	Operating
Max Tensile Load	1,400 N (310 lbs)	450 N 100 (lbs)
Min Bend Radius	8.6 cm (3.4 in)	5.7 cm (2.2 in)

Outer Jacket Properties
Oil Resistant per UL 1581, Table 50.182
Sunlight Resistant per UL 444, Section 7.22
Abrasion Resistant per UL 2556, Section 7.10

Mechanical and Environmental	
Impact Resistance EIA/TIA-455-25A	1,500 Impacts
Crush Resistance TIA/EIA-455-41A	1,800 N/cm
Operating Temperature	-40°C to +85°C
Storage Temperature	-55°C to +85°C
Installation Temperature (actual temp.of cable)	-10°C to +60°C
Flame Retardancy	UL Listed Type OFNR (UL 1666) and FT4 (CSA C22.2 No. 232)

Cable Characteristics	
Jacket Color	Yellow
Jacket Material	Indoor / Outdoor PVC
Buffer Material	PVC
Cable Weight	31 kg/km (21 lbs/1000')
Cable Diameter	5.7 mm (0.22 in)

Electrical and Electronic Wire & Cable • Enterprise Cabling & Security Solutions • OEM Supply – Fasteners  
Anixter Inc. World Headquarters • 2301 Patriot Boulevard, Glenview, IL 60026-8020 • 1.800.ANIXTER • 224.521.8000 • anixter.com

Anixter is a leading global distributor of enterprise cabling and security solutions, electrical and electronic wire and cable, and OEM supply – fasteners and other small parts.  
We reduce risk, complexity and cost from our customers' purchasing decisions, business processes and supply chains.

Anixter does not manufacture these products. Any product warranties are provided by the applicable manufacturers. Data and suggestions made are not to be construed as recommendations to purchase or as authorizations to use any products in violation of any law or regulation. TO THE FULLEST EXTENT PERMITTED BY LAW, ANIXTER DISCLAIMS ALL WARRANTIES, EITHER EXPRESS OR IMPLIED. ANIXTER MAKES NO WARRANTY OR REPRESENTATION, EXPRESS OR IMPLIED, ABOUT THE ACCURACY OR COMPLETENESS OF ANY INFORMATION PROVIDED.