



F112KLS3
FlexTwist™ Flexible Twist for WR112, 7.05–10.0 GHz, with interface types PBR84 and UDR84, 900 mm

Electrical Specifications

Operating Frequency Band	7.05 – 10.0 GHz
Attenuation	0.40 db/m 0.12 db/ft
Average Power	1260 W
Peak Power	315.0 kW
VSWR	1.10


General Specifications

Component	Flexible Twist
Waveguide Size	WR112 WG15 R84
Interface	PBR84
Interface 2	UDR84
Length	900 mm 35 in


Mechanical Specifications

Maximum Twist	264.00 °/m 80.00 °/ft
Minimum Bend Radius, Multiple Bends (E Plane)	76.00 mm 3.00 in
Minimum Bend Radius, Multiple Bends (H Plane)	152.00 mm 6.00 in
Pressurization, maximum	35 psi 240 kPa


Component



Interface



Interface 2



Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU
China RoHS SJ/T 11364-2006
ISO 9001:2008

Classification

Compliant by Exemption
Above Maximum Concentration Value (MCV)
Designed, manufactured and/or distributed under this quality management system

Product Specifications

COMMScope®

F112KLS3

POWERED BY

