



LNX-6514DS-T6M

Andrew® Antenna, 698–896 MHz, 65° horizontal beamwidth, fixed electrical tilt

- Broadband, providing future-ready single antenna for application in 700 MHz and existing 850 MHz cellular operation
- Air dielectric design provides superior PIM performance with repeatable antenna-to-antenna gain and pattern consistency
- Single piece radome provides long term mechanical stability
- Proven core design technology, with over 1,000,000 similar antennas deployed
- Exceptional USLS pattern shaping for optimizing coverage and interference mitigation for LTE applications
- Specifically designed to have physical dimensions similar to most existing cellular antennas

OBSOLETE

This product was discontinued on: **May 31, 2014**

Replaced By

LNX-6514DS-VTM

Andrew® Antenna, 698–896 MHz, 65° horizontal beamwidth, RET compatible

Electrical Specifications

Frequency Band, MHz	698–806	806–896
Gain, dBi	15.8	16.6
Beamwidth, Horizontal, degrees	65	65
Beamwidth, Vertical, degrees	12.6	11.0
Beam Tilt, degrees	6	6
USLS, typical, dB	18	18
Front-to-Back Ratio at 180°, dB	34	34
Isolation, dB	30	30
VSWR Return Loss, dB	1.35 16.5	1.35 16.5
PIM, 3rd Order, 2 x 20 W, dBc	-150	-150
Input Power per Port, maximum, watts	500	500
Polarization	±45°	±45°
Impedance	50 ohm	50 ohm

General Specifications

Antenna Brand	Andrew®
Antenna Type	DualPol®
Band	Single band
Brand	DualPol®
Operating Frequency Band	698 – 896 MHz

Mechanical Specifications

Color	Light gray
Lightning Protection	dc Ground
Radiator Material	Aluminum
Radome Material	Fiberglass, UV resistant

INX-6514DS-T6M



RF Connector Interface	7-16 DIN Female
RF Connector Location	Bottom
RF Connector Quantity, total	2
Wind Loading, maximum	617.7 N @ 150 km/h 138.9 lbf @ 150 km/h
Wind Speed, maximum	241.0 km/h 149.8 mph

Dimensions

Depth	181.0 mm 7.1 in
Length	1847.0 mm 72.7 in
Width	301.0 mm 11.9 in
Net Weight	17.4 kg 38.4 lb

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant by Exemption
China RoHS SJ/T 11364-2006	Above Maximum Concentration Value (MCV)
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system



Included Products

DB380 — Pipe Mounting Kit for 2.4"-4.5" (60-115mm) OD round members on wide panel antennas. Includes 2 clamp sets and double nuts.

DB5083 — Downtilt Mounting Kit for 2.4"-4.5" (60 - 115 mm) OD round members. Includes a heavy-duty, galvanized steel downtilt mounting bracket assembly and associated hardware. This kit is compatible with the DB380 pipe mount kit for panel antennas that are equipped with two mounting brackets.