



## LM-100-SSH

Tapered Pipe-to-Pipe Adapter, adapts 4 in to 9 in OD pipe to 8 in to 16 in OD pipe

### Dimensions

Mounting Diameter, maximum	228.6 mm		9 in
Mounting Diameter, minimum	101.6 mm		4 in
Height	50.8 mm		2.0 in
Length	762.0 mm		30.0 in
Mounting Diameter 2, maximum	406.4 mm		16 in
Mounting Diameter 2, minimum	203.2 mm		8 in
Weight	29.9 kg		66.0 lb
Width	508.0 mm		20.0 in

### General Specifications

Product Type	Clamp set
Tower Taper	Tapered
Includes	Clamp halves   Threaded rod
Material Type	Hot dip galvanized steel
Mounting	Pipe-to-pipe
Package Quantity	2

### Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system