



CM-60S-72

Chain Mount Kit, 16 ft chain, includes pipe

Dimensions

Mounting Diameter, maximum	1524.0 mm		60 in
Mounting Diameter, minimum	203.2 mm		8 in
Pipe Outer Diameter	60.3 mm		2 3/8 in
Height	152.4 mm		6.0 in
Length	1828.8 mm		72.0 in
Mounting Circumference, maximum	4775.2 mm		188.0 in
Mounting Circumference, minimum	635.0 mm		25.0 in
Weight	27.1 kg		59.8 lb
Width	203.2 mm		8.0 in

Environmental Specifications

Man Rating	250 lb vertical man load at 15 mph (BWS)
Wind Rating	120 mph (BWS) at 100 ft AGL
Wind Rating Criteria	One 96 in x 10 in panel antenna per sector
Wind Rating Test Method	TIA/EIA-222

General Specifications

Product Type	Chain mount
Pipe Length	1828.8 mm 72.0 in
Pipe, quantity	1
Chain Length	4.9 m 16.0 ft
Chains, quantity	2
Includes	Chains Plain end pipes
Material Type	Hot dip galvanized steel
Package Quantity	1
Sectors, quantity	1

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system

Included Products

MT-651 — Plain End Pipe, 2-3/8 in OD x 72 in

Product Specifications

COMMScope®

CM-60S-72



CM-60S-B — Chain Mount Base Kit, 16 ft chain

* Footnotes

Man Rating	BWS—Base Wind Speed
Wind Rating	BWS—Base Wind Speed; FBC—Florida Building Code