



## MC-PK14L-B

**Low-Profile Co-location Platform Kit, 14 ft face, 30 in to 60 in OD**

### Dimensions

|                                 |                      |
|---------------------------------|----------------------|
| Face Width                      | 4.4 m   14.5 ft      |
| Mounting Diameter, maximum      | 1524.0 mm   60 in    |
| Mounting Diameter, minimum      | 762.0 mm   30 in     |
| Pipe Outer Diameter             | 60.3 mm   2 3/8 in   |
| Height                          | 254.0 mm   10.0 in   |
| Length                          | 914.4 mm   36.0 in   |
| Mounting Circumference, maximum | 4785.4 mm   188.4 in |
| Mounting Circumference, minimum | 2392.7 mm   94.2 in  |
| Weight                          | 684.9 kg   1510.0 lb |
| Width                           | 4419.6 mm   174.0 in |

### Environmental Specifications

|                                    |  |
|------------------------------------|--|
| EPA with 1/2 in (12 mm) radial ice | 1.2 m <sup>2</sup>   13.1 ft <sup>2</sup>  |
| EPA without ice                    | 0.9 m <sup>2</sup>   10.2 ft <sup>2</sup>  |
| Man Rating                         | 250 lb vertical man load at 15 mph (BWS)   |
| Wind Rating                        | 120 mph (BWS) at 150 ft AGL   140 mph (3-second gust) at 150 ft AGL using Exposure D per FBC |
| Wind Rating Test Method            | TIA/EIA-222  |


### General Specifications

|                   |                                     |
|-------------------|-------------------------------------|
| Product Type      | Co-location platform                |
| Pipe, quantity    | 0                                   |
| Includes          | Pipe mounts   Platform   Ring mount |
| Material Type     | Hot dip galvanized steel            |
| Mounting          | Monopole, 762–1524 mm (30–60 in) OD |
| Package Quantity  | 1                                   |
| Sectors, quantity | 3                                   |

MC-PK14LB



## Outline Drawing



## Regulatory Compliance/Certifications

| Agency        | Classification   |
|---------------|--|
| ISO 9001:2008 | Designed, manufactured and/or distributed under this quality management system |

## Included Products

MT-196-14L — Low Profile Co-location Platform, 14 ft face

MC-RM3060-3 — Universal Ring Mount, 30 in to 60 in OD

## \* Footnotes

|                                 |  |
|---------------------------------|--|
| EPA with 1/2 (12 mm) radial ice | EPA—Effective Projected Area                   |
| EPA without ice                 | EPA—Effective Projected Area                   |
| Man Rating                      | BWS—Base Wind Speed                            |
| Wind Rating                     | BWS—Base Wind Speed; FBC—Florida Building Code |