

POWERED BY



MRO50-81046

High-pressure Desiccant Dehydrator, 19 in rack mountable, 3.0–5.0 psig, 240 Vac, 50/60 Hz

- To meet our global customer's RoHS environmental needs, we have changed our desiccant to a cobalt-chloride free desiccant. Orange color when dry, turns green when saturated.

COMMScope®

POWERED BY


[illegible]

MR050-81046

POWERED BY



Outline Drawing-Side



Product Specifications


COMMScope®

MR050-81046

POWERED BY




Outline Drawing-Top



MR050-81046



Outline Drawing-Section



Alarm

Low-Pressure Alarm	Factory set
--------------------	-------------

Dimensions

Net Weight	10.3 kg		22.6 lb
Product Depth	228.6 mm		9.0 in
Product Height	177.8 mm		7.0 in
Product Width	482.6 mm		19.0 in
Gross Weight, Packed	11.8 kg		26.0 lb
Product Depth, Packed	584.2 mm		23.0 in
Product Height, Packed	304.8 mm		12.0 in
Product Width, Packed	457.2 mm		18.0 in

Electrical Specifications

Power Cord	Europe power cord with stripped leads
Voltage	240 Vac \pm 10%
Power Consumption, average	11.0 W
Power Frequency	60/50 Hz
Power Phase	Single
Suggested Circuit Breaker Size	15 A

MR050-81046



General Specifications

Dehydrator Type	Desiccant
Voltage Type	ac
Volume Capacity, minimum	0.0 L 0.0 ft³
Volume Capacity, maximum	283.2 L 10.0 ft³
Dew Point	-36 °C (-33 °F)
Flow Rate	0.1 SCFM 1.4 SLPM
Includes	3/8 in polyethylene tubing Drill template Instruction sheet Male connector fitting Power cord Power cord connector lock PTFE tape Screws Street tee fitting
Port Type	3/8 in PE tube
Rack Type	EIA 19 in

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system