



F034MMS2
FlexTwist™ Flexible Twist for WR34, 22.0–33.0 GHz, with interface types UBR260 and UBR260, 600 mm

Electrical Specifications

Operating Frequency Band	22.0 – 33.0 GHz
Attenuation	0.90 db/ft 2.95 db/m
Average Power	75 W
Peak Power	20.0 kW
VSWR	1.20


General Specifications

Component	Flexible Twist
Waveguide Size	WR34 WG21 R260
Interface	UBR260
Interface 2	UBR260
Length	600 mm 24 in

Mechanical Specifications

Maximum Twist	510.00 °/m 155.00 °/ft
Minimum Bend Radius, Multiple Bends (E Plane)	38.00 mm 1.50 in
Minimum Bend Radius, Multiple Bends (H Plane)	76.00 mm 3.00 in
Pressurization, maximum	45 psi 310 kPa


Component



Interface



Interface 2



Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU
China RoHS SJ/T 11364-2006
ISO 9001:2008

Classification

Compliant by Exemption
Above Maximum Concentration Value (MCV)
Designed, manufactured and/or distributed under this quality management system

Product Specifications

COMMScope®

F034MMS2

POWERED BY

