

MT-196

Low Profile Co-location Platform, 12 ft face

Dimensions

| | |
|----------------------------|----------------------|
| Face Width | 3.8 m 12.5 ft |
| Mounting Diameter, maximum | 762.0 mm 30 in |
| Mounting Diameter, minimum | 254.0 mm 10 in |
| Height | 254.0 mm 10.0 in |
| Length | 914.4 mm 36.0 in |
| Weight | 509.5 kg 1123.2 lb |
| Width | 3810.0 mm 150.0 in |

Environmental Specifications

| | |
|------------------------------------|--|
| EPA with 1/2 in (12 mm) radial ice | 1.0 m ² 11.3 ft ² |
| EPA without ice | 0.8 m ² 8.8 ft ² |
| Man Rating | 250 lb vertical man load at 15 mph (BWS) |
| Wind Rating | 120 mph (BWS) at 150 ft AGL 140 mph (3-second gust) at 150 ft AGL using Exposure D per FBC |
| Wind Rating Criteria | Four 72 in x 8 in panel antennas per sector |
| Wind Rating Test Method | TIA/EIA-222 |

General Specifications


| | |
|-------------------|--------------------------|
| Product Type | Co-location platform |
| Includes | Platform |
| Material Type | Hot dip galvanized steel |
| Mounting | Ring mount |
| Package Quantity | 1 |
| Sectors, quantity | 3 |

MT-196

POWERED BY



Outline Drawing



Regulatory Compliance/Certifications

| Agency | Classification |
|---------------|--|
| ISO 9001:2008 | Designed, manufactured and/or distributed under this quality management system |

* Footnotes

| | |
|------------------------------------|--|
| EPA with 1/2 in (12 mm) radial ice | EPA—Effective Projected Area |
| EPA without ice | EPA—Effective Projected Area |
| Man Rating | BWS—Base Wind Speed |
| Wind Rating | BWS—Base Wind Speed; FBC—Florida Building Code |