



MT-196-14L  
Low Profile Co-location Platform, 14 ft face

## Dimensions

Face Width	4.4 m   14.5 ft
Mounting Diameter, maximum	1524.0 mm   60 in
Mounting Diameter, minimum	762.0 mm   30 in
Height	254.0 mm   10.0 in
Length	914.4 mm   36.0 in
Weight	581.0 kg   1280.8 lb
Width	4419.6 mm   174.0 in

## Environmental Specifications

EPA with 1/2 in (12 mm) radial ice	1.2 m <sup>2</sup>   13.1 ft <sup>2</sup>
EPA without ice	0.9 m <sup>2</sup>   10.2 ft <sup>2</sup>
Man Rating	250 lb vertical man load at 15 mph (BWS)
Wind Rating	120 mph (BWS) at 150 ft AGL   140 mph (3-second gust) at 150 ft AGL using Exposure D per FBC
Wind Rating Criteria	Four 72 in x 8 in panel antennas per sector
Wind Rating Test Method	TIA/EIA-222


## General Specifications

Product Type	Co-location platform
Includes	Platform
Material Type	Hot dip galvanized steel
Mounting	Ring mount
Package Quantity	1
Sectors, quantity	3

MT-196-14L



## Outline Drawing



## Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system

### \* Footnotes

EPA with 1/2 in (12 mm) radial ice	EPA—Effective Projected Area
EPA without ice	EPA—Effective Projected Area
Man Rating	BWS—Base Wind Speed
Wind Rating	BWS—Base Wind Speed; FBC—Florida Building Code