



MT-198

Double Pipe Support Arm with U-bolts, 63 in

Dimensions

Pipe Outer Diameter	114.3 mm 4 1/2 in
Height	406.4 mm 16.0 in
Length	1600.2 mm 63.0 in
Weight	46.7 kg 102.9 lb
Width	254.0 mm 10.0 in

Environmental Specifications

Man Rating	250 lb vertical man load at 15 mph (BWS)
Wind Rating	120 mph (BWS) at 150 ft AGL 140 mph (3-second gust) at 150 ft AGL using Exposure D per FBC
Wind Rating Criteria	Four 72 in x 8 in panel antennas per sector
Wind Rating Test Method	TIA/EIA-222

General Specifications

Product Type	Universal ring mount
Includes	Hardware Stand-off arms
Material Type	Hot dip galvanized steel
Mounting	Ring mount
Package Quantity	1
Stand-off Distance	1600.2 mm 63.0 in

Outline Drawing

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system

* Footnotes

Man Rating	BWS—Base Wind Speed
Wind Rating	BWS—Base Wind Speed; FBC—Florida Building Code