

POWERED BY



ODPMT200-89015


DryLine® Dehydrator, membrane, outdoor pole/slab mountable, 5.0 psig, with summary alarm, 115 Vac, 50/60 Hz

ODPMT200-89015

POWERED BY



Outline Drawing-Front




ODPMT200-89015

POWERED BY



Outline Drawing–Front Open




ODPMT200-89015

POWERED BY



Outline Drawing-Side




ODPMT200-89015

POWERED BY




Outline Drawing-Back



ODPMT200-89015



Outline Drawing-Section



Alarm

Alarm Type	Summary
Low-Pressure Alarm	68 mbar 7 kPa 1 psig

Dimensions

Net Weight	22.8 kg 50.3 lb
Product Depth	254.0 mm 10.0 in
Product Height	812.8 mm 32.0 in
Product Width	482.6 mm 19.0 in
Gross Weight, Packed	42.3 kg 93.2 lb
Product Depth, Packed	381.0 mm 15.0 in
Product Height, Packed	685.8 mm 27.0 in
Product Width, Packed	660.4 mm 26.0 in

Electrical Specifications

ODPMT200-89015

POWERED BY



Power Cord	USA power cord
Voltage	115 Vac $\pm 10\%$
Alarm Contact Rating	Form C dry contacts, 2 amps at 30 Vdc
Operating Temperature	-34 °C to +54 °C (-30 °F to +130 °F)
Power Consumption, average	254.0 W
Power Frequency	60/50 Hz
Power Phase	Single
Suggested Circuit Breaker Size	15 A
Circuit Breaker Requirement	Electrical connections require separate circuits for dehydrator installation

General Specifications

Dehydrator Type	Automatic Membrane
Voltage Type	ac
Volume Capacity, minimum	0.3 L 0.0 ft ³
Volume Capacity, maximum	1699.0 L 60.0 ft ³
Brand	DryLine®
Dew Point	Better than -45 °C (-50 °F) at 95% RH at +40 °C (+104 °F)
Flow Rate	0.2 SCFM 5.7 SLPM
Includes	3/8 in polyethylene tubing 90° elbow fitting Flat washers Hex nuts Instruction sheet Lock washers Male connector fitting PTFE tape Screws
Mount Type	Pole Slab
Port Count	2
Port Type	3/8 in PE tube
Regulated Output Pressure Type	factory set
Regulated Output Pressure, maximum	5.0 psig

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system