

Product Specifications



F112CHA2

Flexible Twist for WR112, 7.125–7.75 GHz, with interface types CPR112G and PDR84, 600 mm



CHARACTERISTICS

Electrical Specifications

Operating Frequency Band	7.125 – 7.75 GHz
Attenuation	0.40 db/m 0.12 db/ft
Average Power	1260 W
Peak Power	315.0 kW
VSWR	1.03

General Specifications

Component	Flexible Twist
Waveguide Size	WR112 WG15 R84
Interface	CPR112G
Interface 2	PDR84
Length	600 mm 24 in

Mechanical Specifications

Maximum Twist	264.00 °/m 80.00 °/ft
Minimum Bend Radius, Multiple Bends (E Plane)	76.00 mm 3.00 in
Minimum Bend Radius, Multiple Bends (H Plane)	152.00 mm 6.00 in
Pressurization, maximum	35 psi 240 kPa

Component

Interface

Interface 2




www.commscope.com/andrew

©2011 CommScope, Inc. All rights reserved.
All trademarks identified by ® or ™ are registered trademarks or trademarks, respectively, of CommScope. All specifications are subject to change.
See www.commscope.com/andrew for the most current information.

page 1 of 2
5/2/2011

Product Specifications

F112CHA2



Regulatory Compliance/Certifications

Agency

RoHS 2002/95/EC

China RoHS SJ/T 11364-2006

ISO 9001:2008

Classification

Compliant by Exemption

Above Maximum Concentration Value (MCV)

Designed, manufactured and/or distributed under this quality management system



www.commscope.com/andrew

©2011 CommScope, Inc. All rights reserved.

All trademarks identified by ® or ™ are registered trademarks or trademarks, respectively, of CommScope. All specifications are subject to change. See www.commscope.com/andrew for the most current information.

page 2 of 2
5/2/2011