



PM-412-63
Adjustable Pipe Mount, 4-1/2 in OD x 63 in

Dimensions

Pipe Outer Diameter	114.3 mm 4 1/2 in
Height	1600.2 mm 63.0 in
Length	152.4 mm 6.0 in
Weight	25.9 kg 57.1 lb
Width	152.4 mm 6.0 in

Environmental Specifications

Wind Rating	120 mph (BWS) at 150 ft AGL
Wind Rating Test Method	TIA/EIA-222

General Specifications


Product Type	Pipe mount
Pipe Length	1600.2 mm 63.0 in
Pipe, quantity	1
Tower Taper	Non-tapered
Includes	Brackets Hardware Pipe
Material Type	Hot dip galvanized steel
Mounting	Saddle mounts
Note	One 96 in x 8 in panel antenna per pipe mount
Package Quantity	1

PM-412-63

POWERED BY



Outline Drawing



Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system

Included Products

MT-653-63 — Plain End Pipe, 4-1/2 in OD x 63 in

* Footnotes

Wind Rating BWS—Base Wind Speed; FBC—Florida Building Code